

T-200-UW-NMI6

Low PIM Termination 200 W Load, 0-6000MHz



OBSOLETE

This product was discontinued on: October 30, 2022

Replaced By:

T-200-UW-43-M-I6

Low PIM Termination 200 W Load, 0-6000MHz

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type

Termination Load

General Specifications

Device Type

Termination Load

Application

Indoor/Outdoor

Color

Silver

Inner Contact Plating

Silver

Interface

N Male

Outer Contact Plating

Trimetal

Dimensions

Height

126 mm | 4.961 in

Width

130 mm | 5.118 in

Length

232 mm | 9.134 in

Electrical Specifications

3rd Order IMD

-163 dBc

3rd Order IMD Test Method


Two +43 dBm carriers

T-200-UW-NMI6

Average Power, maximum	200 W
Impedance	50 ohm
Operating Frequency Band	0 – 6000 MHz
VSWR at Frequency Band	1.2:1 @ 0–555 MHz 1.2:1 @ 555–2700 MHz 1.3:1 @ 2700–6000 MHz

T-200-UW-NMI6

Derating Curve



Environmental Specifications

Operating Temperature	-25 °C to +50 °C (-13 °F to +122 °F)
Relative Humidity	Up to 100%
Ingress Protection Test Method	IEC 60529:2001, IP65

Packaging and Weights

Height, packed	200 mm 7.874 in
Width, packed	200 mm 7.874 in
Length, packed	400 mm 15.748 in
Weight, gross	5 kg 11.023 lb
Weight, net	4.55 kg 10.031 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

T-200-UW-NMI6

