


# MLOC5-RGXF-3M5



HELIAX® M-LOC Multiport cluster 5 ports SureFlex® cable assembly with interface type M-LOC female to open end, size 0.141", length 3.5 meters

## Product Classification

|                |  |
|----------------|--|
| Product Type   | HELIAX® MLOC cluster, SureFlex® D-CLASS, dynamic PIM |
| Product Brand  | HELIAX®   SureFlex®                                  |
| Product Series | MLOC   |

## General Specifications

|                                    |                  |
|------------------------------------|------------------|
| Attachment, Connector A            | Factory attached |
| Body Style, Connector A            | Straight         |
| Interface, Connector A             | M-LOC Female     |
| Specification Sheet Revision Level | A                |

## Dimensions

|              |                   |
|--------------|-------------------|
| Length       | 3.5 m   11.483 ft |
| Nominal Size | 0.141 in          |

## Electrical Specifications

|                                   |                                    |
|-----------------------------------|------------------------------------|
| 3rd Order IMD Dynamic             | -119 dBm                           |
| 3rd Order IMD Dynamic Test Method | Two +43 dBm carriers per IEC 62037 |

## VSWR/Return Loss

| Frequency Band | Gated VSWR | Gated Return Loss (dB) |
|----------------|------------|------------------------|
| 1000–3000 MHz  | 1.07       | 30                     |
| 3000–4200 MHz  | 1.11       | 26                     |
| 4200–5000 MHz  | 1.12       | 25                     |

## Mechanical Specifications

|                                     |                  |
|-------------------------------------|------------------|
| Minimum Bend Radius, multiple Bends | 40 mm   1.575 in |
| Minimum Bend Radius, single Bend    | 8 mm   0.315 in  |

# MLOC5-RGXF-3M5

---

## Environmental Specifications

|                          |   |
|--------------------------|---|
| Installation temperature | -55 °C to +85 °C (-67 °F to +185 °F)          |
| Operating Temperature    | -55 °C to +85 °C (-67 °F to +185 °F)          |
| Storage Temperature      | -55 °C to +85 °C (-67 °F to +185 °F)          |
| Immersion Test Method    | Meets IEC 60529:2001, IP68 in mated condition |

## Regulatory Compliance/Certifications

| Agency     | Classification   |
|------------|--|
| CHINA-ROHS | Below maximum concentration value  |
| REACH-SVHC | Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a> |
| ROHS       | Compliant  |
| UK-ROHS    | Compliant  |

