## 760237767 | UNJ500-P.WH



M-Series Modular Jack, RJ45, Cat5e Unshielded, ProWhite

### Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Modular jack
Product Series	UNJ Series
General Specifications	
ANSI/TIA Category	5e
Cable Type	Unshielded
Color	Pro white
Conductor Type	Solid   Stranded
Integrated Dust Cover Type	None
Mounting	M Series faceplates and panels
Mounting Note	Color matches with M-series Pro white Faceplates
Outlet Feature	Inverted jack face
Outlet Type	Standard
Termination Tool	SL Termination tool
Termination Type	IDC
Transmission Standards	ANSI/TIA-568-C.2   ISO/IEC 11801 Class D
Wiring	T568A   T568B
Dimensions	
Panel Thickness, recommended	1.6 mm   0.063 in
Compatible Insulated Conductor Diameter, maximum	1.45 mm   0.057 in
Contact Plating Thickness	1.27 µm
Compatible Conductor Gauge, solid	24-22 AWG
Compatible Conductor Gauge, stranded	26-24 AWG

Page 1 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 28, 2025



# 760237767 | UNJ500-P.WH

### Electrical Specifications

Remote Powering	Fully supports the safe delivery of power over LAN cabling described by IEEE 802.3bt (Type 4) and complies with the unmating under electrical load requirements prescribed by IEC 60512-99-002
PoE Durability	Supports IEEE 802.3bt Type 4 (90 W) applications greater than 3000 plug to jack mating cycles
Material Specifications	
Contact Base Material	Beryllium copper
Contact Plating Material	Gold
Mechanical Specifications	
Plug to Jack Mating Cycles	Complies to IEC 60603-7 series
Environmental Specifications	
Flammability Rating	UL 94 V-0
Packaging and Weights	
Packaging quantity	1
Packaging Type	Bag

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 2 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 28, 2025

