
	4			3	
Γ	THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	-,	
	© 2016 Commscope, INC. Confidential	NDTICE: These drawings and specifications are the proprietary property of COMMSCOPE, INC. and may be used only for the specific purpose authorized in writing by COMMSCOPE, INC.			



## <u>NOTES:</u>

D

С

В

А

- 1 ATTENUATION  $\leq$  0,3dB, MEASURED AT 1300nm ACC. TO I.E.C. 61300-3-4 METHOD B
- 2 TEST RESULT SHEET SUPPLIED WITH EACH INDIVIDUALLY PACKED ASSEMBLY
- INFO ON LABEL INSIDE THE BAG:
  - BARCODE
  - UNIQUE SERIAL NUMBER
  - COMMSCOPE PART NUMBER
  - FACTORY ORDER NUMBER

## 4 CABLE INFORMATION:

- CORE DIAMETER: 50/125µm
- OUTER JACKET DIAMETER: 0,9mm
- OUTER JACKET COLOUR: GREEN
- OUTER JACKET MATERIAL: LSZH

	2			1	
		H –	REVISION		
			LTR DESCRIPTION D ECN8000019319 - REBRANDI		
					D
	$\left(\begin{array}{c}1\end{array}\right)$				
	V			]	
				-	
					С
					2
					6536975
					B
STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850					
PART NUMBER "L" (meter)   X-6536975-Y XY,0					
	3 1 FOAC INFORMATION				
	L FOCAB 0,9S 50/1	<u>ne piece,</u> 25, green	MULTI MODE, BEIGE LSZH		
	Qty Description This drawing is a controlled docum	ENT. DWN R. COOLEN	01AUG2007	ltem	_
	DIMENSIONS: TOLERANCES UNLES OTHERWISE SPECIFI		10AUG2007	MMSCOPE, INC.	
		APVD A. HENGELN PRODUCT SPEC	MOLEN	– 150 PIGTAIL 0,9S LC/PC	
	$ \begin{array}{c} \begin{array}{c} 1 & \text{PLC} & \pm & - \\ 2 & \text{PLC} & \pm & - \\ 2 & \text{PLC} & \pm & - \\ 3 & \text{PLC} & \pm & - \\ 4 & \text{PLC} & \pm & - \\ 4 & \text{PLC} & \pm & - \\ 4 & \text{NGLES} & \pm & - \\ \end{array} $			_	то
		WEIGHT		•6536975 —	
		CUSTOMER		SCALE NTS SHEET 1 OF 1 REV D	