760246051 | P-288-MP-8G1-F12YL/20T



Fiber indoor cable, Plenum MPO Trunk, 288 fiber multi-unit with 12 fiber subunits, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series P-MP

General Specifications

 Cable Type
 MPO trunk cable

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Yellow

Jacket Marking Feet

Subunit, quantity 24

Fibers per Subunit, quantity 12

Total Fiber Count 288

Dimensions


Buffer Tube/Subunit Diameter 2 mm | 0.079 in

Diameter Over Jacket 14.1 mm | 0.555 in

Representative Image



760246051 | P-288-MP-8G1-F12YL/20T



Mechanical Specifications

Minimum Bend Radius, loaded 212 mm | 8.346 in

Minimum Bend Radius, unloaded 141 mm | 5.551 in

Tensile Load, long term, maximum 200 N | 44.962 lbf

Tensile Load, short term, maximum 667 N | 149.948 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 95 m | 311.68 ft

Optical Specifications

Fiber Type G.657.A2/B2

Environmental Specifications

Installation temperature 0 °C to +70 °C (-32 °F to +158 °F)

COMMSCOPE®

Page 2 of 5

760246051 | P-288-MP-8G1-F12YL/20T

Operating Temperature 0 °C to +70 °C (+32 °F to +158 °F)

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing

NEC OFNP (ETL) and c(ETL)

Flame Test Method

NFPA 130 | NFPA 262

Environmental Test Specifications

Heat Age 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend 0 °C to +70 °C (+32 °F to +158 °F)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle 0 °C to +70 °C (+32 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 215 kg/km | 144.473 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant UK-ROHS Compliant



Included Products

CS-8G1-MP – Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T

G.657.A2, B2)

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



CS-8G1-MP

Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G. 657.A2, B2)

Product Classification

 Portfolio
 CommScope®

 Product Type
 Optical fiber

General Specifications

Cladding Diameter 125 µm **Cladding Diameter Tolerance** ±0.3 µm Cladding Non-Circularity, maximum 0.7 % **Coating Diameter (Colored)** 249 µm **Coating Diameter (Uncolored)** 242 µm **Coating Diameter Tolerance (Colored)** ±13 μm **Coating Diameter Tolerance (Uncolored)** ±5 µm Coating/Cladding Concentricity Error, maximum 12 µm Core/Clad Offset, maximum $0.5 \, \mu m$

Proof Test 689.476 N/mm² | 100000 psi

Dimensions

Fiber Curl, minimum 4 m | 13.123 ft

Mechanical Specifications

 Macrobending, 15 mm Ø mandrel, 1 turn
 0.50 dB @ 1,550 nm
 1 0.00 dB @ 1,625 nm

 Macrobending, 20 mm Ø mandrel, 1 turn
 0.10 dB @ 1,550 nm
 0.20 dB @ 1,625 nm

 Macrobending, 30 mm Ø mandrel, 10 turns
 0.03 dB @ 1,550 nm
 0.10 dB @ 1,625 nm

Coating Strip Force, maximum8.9 N | 2.001 lbfCoating Strip Force, minimum1.3 N | 0.292 lbf

Dynamic Fatigue Parameter, minimum 20

Optical Specifications

Cabled Cutoff Wavelength, maximum1260 nmPoint Defects, maximum0.1 dB

COMMSCOPE®

CS-8G1-MP

Zero Dispersion Slope, maximum 0.092 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1324 nmZero Dispersion Wavelength, minimum1302 nm

Optical Specifications, Wavelength Specific

Attenuation, maximum 0.40 dB/km @ 1,310 nm | 0.40 dB/km @ 1,385

nm | 0.40 dB/km @ 1,550 nm | 0.50 dB/km @ 1,625

nm

Dispersion, maximum 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285

nm to 1330 nm at 1310 nm

Index of Refraction 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550

nm

 Mode Field Diameter
 8.6 μm @ 1,310 nm | 9.8 μm @ 1,550 nm

Polarization Mode Dispersion Link Design Value, maximum 0.06 ps/sqrt(km)

Standards Compliance ITU-T G.657.A2 | ITU-T G.657.B2

Environmental Specifications

Heat Aging, maximum 0.05 dB/km @ 85 °C

 Temperature Dependence, maximum
 0.05 dB/km

 Temperature Humidity Cycling, maximum
 0.05 dB/km

Water Immersion, maximum 0.05 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Temperature Dependence, maximum Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

