
		′		⁻ I
ITEM	PART NO.	DESCRIPTION	QTY.	WEIGHT
1	RMSM190.01	ANGLE	6	3.03 LBS
2	RMSM19060.02	PIPE BRACE	4	5.58 LBS
3	RMSM2386001	Vertical Pipe Mount	1	12.98 LBS
4	GWF-03	3/8" GALV FLAT WASHER	3	0.03 LBS
5	GB-03345	3/8" X 3-1/2" GALV BOLT KI	Г 3	0.04 LBS
6	GWF-03	3/8" GALV FLAT WASHER	15	0.01 LBS
7	MTC8196	3/8 X 1-1/4" Carriage Bolt	12	0.007 LBS
8	GWL-03	3/8" GALV LOCK WASHER	12	0.01 LBS
9	GN-03	3/8" GALV HEX NUT	12	0.04 LBS



NOTES: 1. ALL METRIC DIMENSIONS ARE IN BRACKETS.

		3	2		1	
	DE. (7015	REVISIONS		v	DATE
	REV.	ZONE	Description Initial release	B MS	Y 200	DATE 2/09/10
			3			
	4	5	2			
				7 6	1)	9
re the proprie	Song DRAIN BY	: SHET:	PART NUMBER:			

These drawings and specifications are the proprietary property of ANDREW CORPORATION and may be used only for the specific purpose authorized in writing by Andrew Corporation.	DRAWN BY: MSM	SHEET: 1 of 1	PART NUMBER: RM-SM238-60
Andrew Corporation.	CHECKED BY:	SCALE:	DESCRIPTION:
ALL DIMENSIONS ARE IN INCHES U.O.S.	TP	NTS	Tripod Antenna Mount, 2-3/8" OD Pipe
TOLERANCES UNLESS OTHERWISE SPECIFIED:	DATE:	MATERIAL:	DRAWING TYPE:
$.X = \pm .12$ ANGLES $\pm 2^*$ $.XX = \pm .06$ FRACTIONS $\pm 1/32$	02/09/10	A36, A53, A568	ASSEMBLY DRAWING
$.XX = \pm .03$ $.XXX = \pm .03$	REVISION:	FINISH: GALV A123	wy .
REMOVE BURRS AND BREAK EDGES .005	A		WESTCHESTER, IL. 60154
DO NOT SCALE THIS PRINT		54.47 LBS	ANDREW ® U.S.A.