

Fiber OSP cable, PE, Gel-filled Central Tube, All-dielectric, 24 fiber, Multimode OM4, Meters jacket marking, Black jacket color

Product Classification

Regional Availability	Asia Australia/New Zealand
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	O-CN


General Specifications

Cable Type	Central loose tube
Construction Type	Non-armored
Fibers per Subunit, quantity	24
Jacket Color	Black
Jacket Marking	Meters
Subunit Type	Gel-filled
Total Fiber Count	24

Dimensions

Buffer Tube/Subunit Diameter	2.8 mm 0.11 in
Diameter Over Jacket	6 mm 0.236 in

Representative Image



Material Specifications

Jacket Material PE

Mechanical Specifications

Minimum Bend Radius, loaded 120 mm | 4.724 in
Minimum Bend Radius, unloaded 60 mm | 2.362 in
Tensile Load, long term, maximum 300 N | 67.443 lbf
Tensile Load, short term, maximum 1000 N | 224.809 lbf
Compression 15 N/mm | 85.652 lb/in
Compression Test Method IEC 60794-1-2 E3
Flex 25 cycles
Strain See long and short term tensile loads
Strain Test Method IEC 60794-1-2-E1

Optical Specifications

Fiber Type OM4

Optical Specifications, Wavelength Specific

Attenuation, maximum 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

Environmental Specifications

Installation temperature -10 °C to +60 °C (+14 °F to +140 °F)

760249700 | O-024-CN-5X-M24BK/28G/093

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Buried Ducted Outdoor
Water Penetration	24 h
Water Penetration Test Method	IEC 60794-1 F5C

Environmental Test Specifications

Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	IEC 60794-1-2 F1

Packaging and Weights

Cable weight	35 kg/km 23.519 lb/kft
---------------------	--------------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable