



Fiber OSP cable, PE, Stranded Loose Tube Gel-filled, 48 fiber, Multimode OM3, Meters jacket marking, Black jacket color

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber OSP cable
<b>Product Series</b>	O-LN


## General Specifications

<b>Cable Type</b>	Stranded loose tube
<b>Construction Type</b>	Non-armored
<b>Subunit Type</b>	Gel-filled
<b>Filler, quantity</b>	2
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Subunit, quantity</b>	4
<b>Fibers per Subunit, quantity</b>	12
<b>Total Fiber Count</b>	48

## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	2.2 mm   0.087 in
<b>Diameter Over Jacket</b>	10.5 mm   0.413 in

## Representative Image



## Material Specifications

**Jacket Material** High density polyethylene (HDPE)

## Mechanical Specifications

**Minimum Bend Radius, loaded** 210 mm | 8.268 in

**Minimum Bend Radius, unloaded** 105 mm | 4.134 in

**Tensile Load, long term, maximum** 890 N | 200.08 lbf

**Tensile Load, short term, maximum** 2700 N | 606.984 lbf

**Compression** 10 N/mm | 57.101 lb/in

**Compression Test Method** IEC 60794-1-2 E3

**Flex** 25 cycles

**Strain** See long and short term tensile loads

**Strain Test Method** IEC 60794-1-21 E1

## Optical Specifications

**Fiber Type** OM3

## Optical Specifications, Wavelength Specific

**Attenuation, maximum** 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

## Environmental Specifications

**Installation temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Environmental Space** Buried | Ducted | Outdoor

**Water Penetration** 24 h

**Water Penetration Test Method** IEC 60794-1 F5B

## Environmental Test Specifications

**Temperature Cycle** -40 °C to +70 °C (-40 °F to +158 °F)

**Temperature Cycle Test Method** IEC 60794-1-2 F1

## Packaging and Weights

**Cable weight** 86 kg/km | 57.789 lb/kft

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable