



Fiber OSP cable, PE, Loose Tube Gel-filled CST, 48 fiber, Singlemode G.652.D and G.657.A1, Meters jacket marking, Black jacket color

## Product Classification

Regional Availability	Asia   Australia/New Zealand
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	O-LA


## General Specifications

Cable Type	Stranded loose tube
Construction Type	Armored
Subunit Type	Gel-filled
Jacket Color	Black
Jacket Marking	Meters
Fibers per Subunit, quantity	12
Total Fiber Count	48

## Dimensions

Buffer Tube/Subunit Diameter	2.2 mm   0.087 in
Diameter Over Jacket	12.2 mm   0.48 in

## Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded	240 mm   9.449 in
Minimum Bend Radius, unloaded	120 mm   4.724 in
Tensile Load, short term, maximum	2700 N   606.984 lbf
Compression	22 N/mm   125.623 lb/in
Compression Test Method	IEC 60794-1-2 E3
Flex	25 cycles
Strain	See long and short term tensile loads
Strain Test Method	IEC 60794-1-21 E1

Optical Specifications

Fiber Type	G.652.D and G.657.A1   OS2
------------	----------------------------

Optical Specifications, Wavelength Specific

Attenuation, maximum	0.22 dB/km @ 1,550 nm   0.36 dB/km @ 1,310 nm
----------------------	---

Environmental Specifications

Installation temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Buried   Ducted   Outdoor
Water Penetration	24 h
Water Penetration Test Method	IEC 60794-1 F5B

Environmental Test Specifications

Temperature Cycle	-30 °C to +70 °C (-22 °F to +158 °F)
Temperature Cycle Test Method	IEC 60794-1-2 F1

Packaging and Weights

Cable weight	140 kg/km   94.076 lb/kft
--------------	---------------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



\* Footnotes

Operating Temperature	Specification applicable to non-terminated bulk fiber cable
-----------------------	---