## 760251066 | N-048-MP-5G-F16LM/30T/B2



Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk Cable, 48 fiber with 16-fiber, 3.0mm subunits, Gel-free, Multimode OM5, Feet jacket marking, Lime green jacket color, B2ca flame rating

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor cable

**Product Series** N-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

**Subunit Type** Gel-free

Filler, quantity

Jacket Color Lime green

Jacket Marking Feet

Subunit, quantity 3

Fibers per Subunit, quantity 16

Total Fiber Count 48

Dimensions


**Buffer Tube/Subunit Diameter** 3 mm | 0.118 in

**Diameter Over Jacket** 10.6 mm | 0.417 in

Representative Image



# 760251066 | N-048-MP-5G-F16LM/30T/B2



## Mechanical Specifications

Minimum Bend Radius, loaded 159 mm | 6.26 in

Minimum Bend Radius, unloaded 106 mm | 4.173 in

**Tensile Load, long term, maximum** 400 N | 89.924 lbf

**Tensile Load, short term, maximum** 1335 N | 300.12 lbf

**Compression** 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 404 m | 1,325.459 ft

**Optical Specifications** 

Fiber Type OM5, LazrSPEED® wideband

## **Environmental Specifications**

Installation temperature  $0 \,^{\circ}\text{C to} + 50 \,^{\circ}\text{C (+32 °F to} + 122 \,^{\circ}\text{F)}$ Operating Temperature  $0 \,^{\circ}\text{C to} + 60 \,^{\circ}\text{C (+32 °F to} + 140 \,^{\circ}\text{F)}$ 

Page 2 of 5



# 760251066 | N-048-MP-5G-F16LM/30T/B2

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+140 \,^{\circ}\text{F}$ )

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceB2caEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd2EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Dual Rated LSZH/Riser | Low Smoke Zero Halogen (LSZH)

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

**Environmental Test Specifications** 

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

**Heat Age Test Method** IEC 60794-1 F9

Low High Bend0 °C to +50 °C (+32 °F to +122 °F)Low High Bend Test MethodFOTP-37 | IEC 60794-1 E11Temperature Cycle0 °C to +60 °C (+32 °F to +140 °F)

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 101 kg/km | 67.869 lb/kft

#### Included Products

CS-5G-MP – LazrSPEED® OM5 WideBand Multimode Fiber

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable



# LazrSPEED®

#### LazrSPEED® OM5 WideBand Multimode Fiber

#### Product Classification

 Portfolio
 CommScope®

 Product Type
 Optical fiber

General Specifications

**Cladding Diameter** 125 µm **Cladding Diameter Tolerance** ±5 µm Cladding Non-Circularity, maximum 0.7 % **Coating Diameter (Colored)** 254 µm **Coating Diameter (Uncolored)** 242 µm **Coating Diameter Tolerance (Colored)** ±7 µm **Coating Diameter Tolerance (Uncolored)** ±5 µm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 50 µm **Core Diameter Tolerance** ±2.5 µm

**Proof Test** 689.476 N/mm<sup>2</sup> | 100000 psi

Mechanical Specifications

Core/Clad Offset, maximum

 Macrobending, 15 mm Ø mandrel, 2 turns
 0.20 dB @ 850 nm | 0.50 dB @ 1,300 nm

 Macrobending, 30 mm Ø mandrel, 2 turns
 0.10 dB @ 850 nm | 0.30 dB @ 1,300 nm

 Macrobending, 75 mm Ø mandrel, 100 turns
 0.50 dB @ 1,300 nm | 0.50 dB @ 850 nm

1 µm

Coating Strip Force, maximum4.5 N | 1.012 lbfCoating Strip Force, minimum0.9 N | 0.202 lbf

**Dynamic Fatigue Parameter, minimum** 18

Optical Specifications

Numerical Aperture 0.2

**COMMSCOPE®** 

## CS-5G-MP

Numerical Aperture Tolerance ±0.010

Point Defects, maximum 0.15 dB

**Zero Dispersion Slope, maximum (0M5)** -412/(840(1-(λ0/840)^4)) ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1328 nmZero Dispersion Wavelength, minimum1297 nm

### Optical Specifications, Wavelength Specific

**1 Gbps Ethernet Distance** 1,110 m @ 850 nm | 600 m @ 1,300 nm

**10 Gbps Ethernet Distance** 550 m @ 850 nm

**Attenuation, maximum** 1.00 dB/km @ 1,300 nm | 2.20 dB/km @ 953 nm | 3.00 dB/km @

850 nm

**Bandwidth, Laser, minimum** 2,600 MHz-km @ 953 nm | 4,700 MHz-km @ 850 nm | 500 MHz-km

@ 1,300 nm

**Bandwidth, OFL, minimum** 1,950 MHz-km @ 953 nm | 3,500 MHz-km @ 850 nm | 500 MHz-km

@ 1,300 nm

**Index of Refraction** 1.478 @ 1,300 nm | 1.483 @ 850 nm

**Standards Compliance** ANSI/TIA-492AAAF (OM5) | ANSI/TIA-568.3 (OM5) | IEC 60793-2-10,

A1 (OM5) | ISO/IEC 11801-1 cabled optical fiber performance category

OM5

### **Environmental Specifications**

**Heat Aging, maximum** 0.10 dB/km @ 85 °C

Temperature Dependence, maximum 0.1 dB/km
Temperature Humidity Cycling, maximum 0.1 dB/km

Water Immersion, maximum 0.10 dB/km @ 23 °C

### Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

#### \* Footnotes

Temperature Dependence, maximum Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

**COMMSCOPE®**