



OFDC B8G Fiber Optic Splice/Patch Closure, X-press version, Gel Cable sealing, 1 pre-installed 18-fiber splice tray, 8 duplex LC/APC adapters, 20 m drop cable assy, mobra

- Advanced gel sealing technology ensures fast and easy field handling without a need for special tools
- Individual access to drop cable connection area and separate zones for looped cable storage for most cable types
- Compact and modular design suited for wraparound drop cable installation, enabling faster deployments
- Allows easy pass-through cabling and integration of optical components, even at later deployment stages

Product Classification

Regional Availability	Australia/New Zealand
Product Type	Single-ended, rectangular fiber closure
Product Series	OFDC


General Specifications

Cable Ports Quantity, total	4 round ports + 8 round ports
Cable Sealing Type	Compressed gel
Closure Sealing Type	Hinged with latch
Closure Style	Single-ended
Color	Black
Mounting	Manhole Pedestal Strand Wall
Port Type	LC/APC
Splice Tray Included, quantity	1
Splice Tray Type Included	18-way, heat shrink
Splitter Type	No splitter
Splitter, quantity	0

Dimensions

Height	128 mm 5.039 in
Width	156 mm 6.142 in
Length	324 mm 12.756 in

Ordering Tree



Material Specifications

Material Type

Rugged polymer

Environmental Specifications

Installation temperature

-5 °C to +45 °C (+23 °F to +113 °F)

Storage Temperature

-30 °C to +60 °C (-22 °F to +140 °F)

Relative Humidity

93%, non-condensing

Environmental Space

Above ground | Below ground

Qualification Standards

IEC 60529, IP68 + 2 m waterhead

UV Resistance

UV stabilized

Packaging and Weights

Packaging quantity

1

Packaging Type

Box | Carton

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

Classification

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

1155163-2 | OFDC-B8G-RAT-16F-20M-KIT-NZ1

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

