COP1KW2-88F002



CommScope® Category 6A, F/UTP Cord, Shielded, Plenum, RJ45 to Ceiling connector, 2 ft, White

- Perfect solution for connected devices in the ceiling: IP cameras, Wi-Fi access points and inbuilding wireless systems, LED lighting and sound masking systems
- For installation in difficult-to-access areas
- Provides a high-quality cable interconnection, available as a standalone unit or pre-terminated to an RJ45 plug
- Category 6A

Product Classification

Regional AvailabilityNorth AmericaPortfolioCommScope®

Product Type Twisted pair patch cord

General Specifications

ANSI/TIA Category 6A

 Cable Type
 F/UTP (shielded)

Conductor Type Solid

Interface, Connector A Ceiling connector

Interface Feature, connector AStandardInterface, Connector BRJ45 plugInterface Feature, connector BStandardJacket ColorWhitePairs, quantity4

Wiring T568B

Dimensions

Cord Length 0.6 m | 1.969 ft

Compatible Conductor Gauge, stranded 24 AWG

Wiring Diagram



COP1KW2-88F002

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

Material Specifications

Contact Plating Material Precious metals

Material Type Copper alloy | High-impact, flame retardant, thermoplastic | Stainless Steel

Contact Spring | Zinc Die Cast Shield

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Plug Retention Force, minimum 133 N | 29.9 lbf

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Relative HumidityUp to 95%, non-condensing

Environmental SpacePlenumFlammability RatingUL 94 V-0Safety StandardETL | cETL

Packaging and Weights

Packaging quantity 2

Regulatory Compliance/Certifications

Agency Classification



COP1KW2-88F002

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

