

# CX3299999 | 100T135 EMPTY DUCT COEX

ConQuest® Empty Conduit, 1 in, SDR 13.5, terracotta



## Product Classification

Product Type	Empty conduit
Product Brand	ConQuest®

## General Specifications

Color	Terracotta
Conduit Type	Non-toneable
Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm³   0.035 lb/in³
Density, minimum	0.941 g/cm³   0.034 lb/in³
Design Standard	ASTM D3350-05
Wall Type	Smooth

## Dimensions

Length	914.4 m   3000 ft
Inner Diameter, nominal	27.965 mm   1.101 in
Outer Diameter, nominal	33.401 mm   1.315 in
Wall Thickness Designation	SDR 13.5
Wall Thickness, minimum	2.464 mm   0.097 in
Nominal Size	1 in

## Material Specifications

Flexural Modulus, minimum	551.581 N/mm²   80000 psi
Flexural Property Test Method	ASTM D790
Hydrostatic Design Basis	Not pressure rated

# CX3299999 | 100T135 EMPTY DUCT COEX

Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE)
Melt Flow Rate Test Method	ASTM D1238
Melt Flow Rate, maximum	0.39 g/10 min

## Mechanical Specifications

Minimum Bend Radius, unsupported	355.6 mm   14 in
Tensile Property Test Method	ASTM D638
Tensile Strength at yield, minimum	20.684 N/mm <sup>2</sup>   3000 psi
Pulling Tension, maximum	358.338 kg   790 lb

## Environmental Specifications

Environmental Stress Crack Resistance	Failure rate of 10% within 96 hours
Environmental Stress Test Method	ASTM D1693, ESCR Condition B

## Packaging and Weights

Weight, net	251.5 kg/km   169 lb/kft
-------------	--------------------------

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

Environmental Stress Crack Resistance	ESCR—Environmental Stress Crack Resistance
---------------------------------------	--