

FEATURES

- Provides amplifier output level stabilization over temperature
- Multiple analog frequency values available
- Two digital frequency values available (QAM ADU)
- QAM ADU utilizes QAM-modulated digital channel as pilot (no need to hold analog channel when expanding digital bandwidth)
- All common ADU models utilize SAW filters to detect pilot signal
- All current ADU models meet FCC and CENELEC requirements

CommScope's automatic drive unit, model ADU-*, and QAM automatic drive unit, model QADU-*, are automatic gain control (AGC) devices. Cable system signal levels vary as cable attenuation and hybrid output vary over temperature. The function of the ADU is to monitor the output level of a selected pilot signal at the output of the host amplifier and send any detected changes in amplitude back to the Bode equalizer. The Bode then makes appropriate corrections in order to adjust the gain of the amplifier to maintain a constant output level for a range of input levels. The ADU/QADU is a plug-in accessory that may be configured into the amplifier (depending on model) or ordered as a separate item for field installation. Use of the ADU/QADU does not reduce station gain.

ADUs and QADUs use surface acoustic wave (SAW) filters to select the pilot frequency. There are several frequency values available: six analog and two digital. For the traditional analog ADUs, the pilot frequency is a continuous wave (CW) signal or an available NTSC television signal not scrambled by the sync suppression method. CommScope also offers a QAM ADU which uses a QAM-modulated digital channel for a pilot signal and supports QAM frequencies at 609 MHz and 711 MHz. This is ideal for cable operators wishing to expand their digital channels below 550 MHz, thereby encroaching into traditional analog space. There is then no need to hold an analog channel. There are two pilot frequency choices available for the QADU, 609 MHz or 711 MHz, which allow most cable operators to carry digital channels at these frequencies. The QAM ADU also offers a gain-hold feature. If the pilot level drops by 20 dB or more, the gain is set to mid-range.

For more information, please contact your CommScope Account Representative.



SPECIFICATIONS

Characteristics	Specification
General	
Pilot Frequency	403.25/S MHz, 427.225/S MHz, 439.25/S MHz, 445.25/S MHz, 499.25/S MHz, 549.00/S MHz, 609.00/S MHz (QAM ADU), and 711.00/S MHz (QAM ADU)
Control Level ("Setting Range")	
F _o = 400–429 MHz	37.0 dBmV (min), 49.0 dBmV (max)
F _o = 430–459 MHz	36.5 dBmV (min), 48.5 dBmV (max)
F _o = 460–505 MHz	36.0 dBmV (min), 48.0 dBmV (max)
F _o = 506–550 MHz	35.5 dBmV (min), 47.5 dBmV (max)
F _o = 609 MHz	38.0 dBmV (min), 48.0 dBmV (max)
F _o = 711 MHz	38.0 dBmV (min), 48.0 dBmV (max)
Pilot Level Accuracy	± 0.4 dB for ± 3 dB change at input
Power Requirements	
IDC	70 mA
AC Power	2.13 W

RELATED PRODUCTS

MB120 Amplifier	BLE120 Amplifier
MB100 Amplifier	BLE100 Amplifier
SFE/SRE Equalizers	BT100 Trunk Amplifier

Contact Customer Care for product information and sales:

- United States: 866-36-ARRIS
- International: +1-678-473-5656

COMMScope®

Note: Specifications are subject to change without notice.

Copyright Statement: © 2022 CommScope, Inc. All rights reserved. ARRIS, the ARRIS logo, and STARLINE are trademarks of CommScope, Inc. and/or its affiliates. All other trademarks are the property of their respective owners. No part of this content may be reproduced in any form or by any means or used to make any derivative work (such as translation, transformation, or adaptation) without written permission from CommScope, Inc. and/or its affiliates ("CommScope"). CommScope reserves the right to revise or change this content from time to time without obligation on the part of CommScope to provide notification of such revision or change.

1514721_ADU_DS_RevA