

# CX3399993 | 125T135WP1800TAPE COEX



ConQuest® Empty Conduit, 1 1/4 in, SDR 13.5, terracotta, with pull tape

## Product Classification

<b>Product Type</b>	Empty conduit
<b>Product Brand</b>	ConQuest®

## General Specifications

<b>Color</b>	Terracotta
<b>Conduit Type</b>	Non-toneable
<b>Density Test Method</b>	ASTM D792A
<b>Density, maximum</b>	0.955 g/cm <sup>3</sup>   0.035 lb/in <sup>3</sup>
<b>Density, minimum</b>	0.941 g/cm <sup>3</sup>   0.034 lb/in <sup>3</sup>
<b>Design Standard</b>	ASTM D3350-05
<b>Wall Type</b>	Smooth

## Dimensions

<b>Length</b>	914.4 m   3000 ft
<b>Inner Diameter, nominal</b>	35.408 mm   1.394 in
<b>Outer Diameter, nominal</b>	42.164 mm   1.66 in
<b>Wall Thickness Designation</b>	SDR 13.5
<b>Wall Thickness, minimum</b>	3.124 mm   0.123 in
<b>Nominal Size</b>	1-1/4 in

## Material Specifications

<b>Flexural Modulus, minimum</b>	551.581 N/mm <sup>2</sup>   80000 psi
<b>Flexural Property Test Method</b>	ASTM D790
<b>Hydrostatic Design Basis</b>	Not pressure rated
<b>Hydrostatic Design Test Method</b>	ASTM D2837
<b>Material Type</b>	High density polyethylene (HDPE)   Polyester
<b>Melt Flow Rate Test Method</b>	ASTM D1238

# CX3399993 | 125T135WP1800TAPE COEX

---

**Melt Flow Rate, maximum** 0.39 g/10 min

## Mechanical Specifications

**Minimum Bend Radius, unsupported** 457.2 mm | 18 in

**Tensile Property Test Method** ASTM D638

**Tensile Strength at yield, minimum** 20.684 N/mm<sup>2</sup> | 3000 psi

**Breaking Strength** 816.466 kg | 1800 lb

**Pull Line Type** Tape

**Pulling Tension, maximum** 571.526 kg | 1260 lb

## Environmental Specifications

**Environmental Stress Crack Resistance** Failure rate of 10% within 96 hours

**Environmental Stress Test Method** ASTM D1693, ESCR Condition B

## Packaging and Weights

**Weight, net** 394.363 kg/km | 265 lb/kft

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## \* Footnotes

**Environmental Stress Crack Resistance** ESCR—Environmental Stress Crack Resistance