

Type N Male for CNT-400 braided cable. Not available in North America.

#### **Product Classification**

Regional Availability

China | EMEA | Europe | Latin America

Product Type Braided cable connector

Product Brand CNT® | ConQuest® | QR®

Ordering Note ANDREW® standard product in Asia Pacific | ANDREW® standard product

in Europe, the Middle East, and Africa

#### General Specifications

Body Style Straight

Inner Contact Attachment Method Captivated

Inner Contact Plating Silver

**Interface** N Male

Outer Contact Attachment Method Crimp

Outer Contact Plating Trimetal

#### **Dimensions**

**Width** 20.25 mm | 0.797 in


**Length** 43 mm | 1.693 in

**Diameter** 20.25 mm | 0.797 in

Nominal Size 0.405 in

#### Outline Drawing





#### **Electrical Specifications**

Insertion Loss, typical 0.05 dB **Cable Impedance** 50 ohm **Connector Impedance** 50 ohm 2500 V dc Test Voltage Inner Contact Resistance, maximum 1 m0hm Insulation Resistance, minimum 5000 MOhm 0 - 6000 MHz **Operating Frequency Band Outer Contact Resistance, maximum** 0.25 m0hm Peak Power, maximum 10 kW RF Operating Voltage, maximum (vrms) 707 V

#### VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
0-3000 MHz	1.036	35.05
3000-6000 MHz	1.152	23.02

### Mechanical Specifications

Connector Retention Tensile Force330 N | 74.187 lbfConnector Retention Torque0.56 N-m | 4.956 in lb

ANDREW®
an Amphenol company

Coupling Nut Proof Torque 1.7 N-m | 15.046 in lb

Coupling Nut Proof Torque Method IEC 61169-16:9.3.6

**Coupling Nut Retention Force** 450 N | 101.164 lbf

**Coupling Nut Retention Force Method** IEC 61169-16:9.3.11

**Interface Durability** 500 cycles

Interface Durability MethodIEC 61169-16:9.5Mechanical Shock Test MethodIEC 60068-2-27

#### **Environmental Specifications**

Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

Storage Temperature  $-65 \,^{\circ}\text{C}$  to  $+125 \,^{\circ}\text{C}$  (-85  $^{\circ}\text{F}$  to  $+257 \,^{\circ}\text{F}$ )

Attenuation, Ambient Temperature $20 \, ^{\circ}\text{C}$  |  $68 \, ^{\circ}\text{F}$ Average Power, Ambient Temperature $40 \, ^{\circ}\text{C}$  |  $104 \, ^{\circ}\text{F}$ Average Power, Inner Conductor Temperature $100 \, ^{\circ}\text{C}$  |  $212 \, ^{\circ}\text{F}$ 

Climatic Sequence Test Method IEC 60068-1

Corrosion Test Method IEC 60068-2-11

Damp Heat Steady State Test Method IEC 60068-2-3

Immersion Depth1 mImmersion Test MatingMated

**Immersion Test Method** IEC 60529:2001, IP68

Thermal Shock Test Method IEC 60068-2-14

Vibration Test Method IEC 60068-2-6

Packaging and Weights

Weight, net  $32.42 \text{ g} \mid 0.071 \text{ lb}$ 

#### Regulatory Compliance/Certifications

AgencyClassificationCHINA-ROHSBelow maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant

UK-ROHS Compliant/Exempted





#### \* Footnotes

**Insertion Loss, typical** 0.05√ freq (GHz) (not applicable for elliptical waveguide)

**Immersion Depth** Immersion at specified depth for 24 hours

