

# H7FB-110-S

---



1-5/8 in EIA Female Flange with gas barrier for 1-5/8 in HJ7-50A air dielectric cable. Coupling Element, O-Ring, screw-set sold separately. Click-on: Related Products, Device connectors and Adapters

## Product Classification

<b>Product Type</b>	Air coaxial connector
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	Gas pass version can be created by drilling out the PTFE dielectric

## General Specifications

<b>Body Style</b>	Straight
<b>Cable Family</b>	HJ7-50A
<b>Gas Barrier</b>	Yes
<b>Inner Contact Attachment Method</b>	Thread-in stub
<b>Inner Contact Plating</b>	Silver
<b>Interface</b>	1-5/8 in EIA Male Flange
<b>Mounting Angle</b>	Straight
<b>Outer Contact Attachment Method</b>	Tab-flare
<b>Outer Contact Plating</b>	Silver

## Dimensions

<b>Length</b>	140.97 mm   5.55 in
<b>Diameter</b>	88.392 mm   3.48 in
<b>Nominal Size</b>	1-5/8 in

## Electrical Specifications

<b>Insertion Loss, typical</b>	0.05 dB
<b>Average Power at Frequency</b>	4.9 kW @ 900 MHz
<b>Cable Impedance</b>	50 ohm

# H7FB-110-S

---

<b>Connector Impedance</b>	50 ohm
<b>dc Test Voltage</b>	11 kV
<b>Insulation Resistance, minimum</b>	5000 MOhm
<b>Operating Frequency Band</b>	0 – 2700 MHz
<b>Peak Power, maximum</b>	300 kW
<b>RF Operating Voltage, maximum (vrms)</b>	3880 V

## VSWR/Return Loss

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
<b>0–1000 MHz</b>	1.02	40.09
<b>1000–2200 MHz</b>	1.04	34.16
<b>2200–2700 MHz</b>	1.06	30.72

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Storage Temperature</b>	-70 °C to +85 °C (-94 °F to +185 °F)

## Packaging and Weights

<b>Weight, net</b>	1.4 kg   3.086 lb
--------------------	-------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant



## \* Footnotes

<b>Insertion Loss, typical</b>	0.05v <sup>-</sup> freq (GHz) (not applicable for elliptical waveguide)
--------------------------------	---