

N-Type Female High Power Termination Load, 70–3000 MHz

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Termination Load


General Specifications

Device Type	Termination Load
Color	Silver
Interface	N Female

Electrical Specifications

Return Loss, minimum	20 dB
Average Power, maximum	175 W
Impedance	50 ohm
Operating Frequency Band	70 – 3000 MHz
Peak Power, maximum	1.5 kW
VSWR	1.22

Derating Curve



Environmental Specifications

Operating Temperature -33 °C to +65 °C (-27.4 °F to +149 °F)

Ingress Protection Test Method IEC 60529:2001, IP30

Packaging and Weights

Height, packed 242 mm | 9.528 in

Width, packed 165 mm | 6.496 in

Length, packed 130 mm | 5.118 in

Weight, gross 3.7 kg | 8.157 lb

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

7651928-01

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

