

4.3-10 Male for 1/2 in LDF4-50A cable

Product Classification

Product Type Wireless and radiating connector

Product Brand HELIAX®

Product Series LDF4-50A

Ordering Note CommScope® standard product (Global)

General Specifications

Body Style Straight

Cable Family LDF4-50A

Inner Contact Attachment Method Captivated

Inner Contact Plating Silver

Interface4.3-10 MaleMounting AngleStraightOuter Contact Attachment MethodClampOuter Contact PlatingTrimetal

Dimensions


Length 51.69 mm | 2.035 in | 73.15 mm | 2.88 in

Diameter 24.89 mm | 0.98 in

Nominal Size 1/2 in

Outline Drawing





Electrical Specifications

3rd Order IMD at Frequency-115 dBm @ 1800 MHz3rd Order IMD Test MethodTwo +43 dBm carriers

Insertion Loss Coefficient, typical 0.05

Average Power at Frequency 600.0 W @ 900 MHz

Cable Impedance 50 ohm **Connector Impedance** 50 ohm dc Test Voltage 2500 V **Inner Contact Resistance, maximum** 1 m0hm 5000 MOhm Insulation Resistance, minimum 0 - 8800 MHz **Operating Frequency Band Outer Contact Resistance, maximum** 1 m0hm 22.5 kW Peak Power, maximum

VSWR/Return Loss

Shielding Effectiveness

RF Operating Voltage, maximum (vrms)

Frequency Band	VSWR	Return Loss (dB)	VSWR, typical	Return Loss, typical (dB)
0-3.8 GHz	1.106	25.96		
3800-6000 MHz			1.26	19

884 V

-110 dB

COMMSCOPE®

Mechanical Specifications

Attachment Durability 25 cycles

Connector Retention Tensile Force 889.64 N | 200 lbf

Connector Retention Torque5.42 N-m | 47.998 in lbCoupling Nut Proof Torque10 N-m | 88.507 in lbCoupling Nut Retention Force449.98 N | 101.16 lbf

Interface Durability 100 cycles

Mechanical Shock Test Method IEC 60068-2-27

Environmental Specifications

Operating Temperature-45 °C to +85 °C (-49 °F to +185 °F)Storage Temperature-55 °C to +85 °C (-67 °F to +185 °F)

Corrosion Test Method IEC 60068-2-11

Immersion Depth 1 m

Immersion Test Method IEC 60529:2001, IP68

Moisture Resistance Test Method IEC 60068-2-3

Thermal Shock Test Method IEC 60068-2-14

Vibration Test Method IEC 60068-2-6

Water Jetting Test Mating Mated

Water Jetting Test Method IEC 60529:2001, IP66

Packaging and Weights

Immersion Test Mating

Weight, net 73.7 g | 0.162 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Mated



* Footnotes

Insertion Loss Coefficient, typical 0.05√ freq (GHz) (not applicable for elliptical waveguide)

COMMSCOPE®

Immersion Depth

Immersion at specified depth for 24 hours

