

# SFX-ADMR

---

7-16 DIN Male Right Angle for 1/2 in SFX-500 cable



**OBSOLETE**

This product was discontinued on: December 2, 2015

## Product Classification

**Product Type** Wireless and radiating connector

## General Specifications

**Body Style** Right angle  
**Cable Family** SFX-500  
**Inner Contact Attachment Method** Captivated  
**Inner Contact Plating** Silver  
**Interface** 7-16 DIN Male  
**Mounting Angle** Right angle  
**Outer Contact Attachment Method** Radial compression  
**Outer Contact Plating** Silver  
**Pressurizable** No

## Dimensions

**Height** 48.26 mm | 1.9 in  
**Length** 53.34 mm | 2.1 in  
**Diameter** 36.07 mm | 1.42 in  
**Nominal Size** 1/2 in

## Electrical Specifications

**3rd Order IMD at Frequency** -115 dBm @ 1800 MHz

# SFX-ADMR

---

<b>3rd Order IMD Test Method</b>	Two +43 dBm carriers
<b>Return Loss Note</b>	Measurements taken using a .9 m (3 ft) jumper assembly
<b>Average Power at Frequency</b>	870.0 W @ 900 MHz
<b>Cable Impedance</b>	50 ohm
<b>Connector Impedance</b>	50 ohm
<b>dc Test Voltage</b>	2500 V
<b>Inner Contact Resistance, maximum</b>	1 mOhm
<b>Insulation Resistance, minimum</b>	5000 MOhm
<b>Operating Frequency Band</b>	0 – 6000 MHz
<b>Outer Contact Resistance, maximum</b>	0.4 mOhm
<b>Peak Power, maximum</b>	15.6 kW
<b>RF Operating Voltage, maximum (vrms)</b>	707 V
<b>Shielding Effectiveness</b>	110 dB

## VSWR/Return Loss

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
<b>0.05–1.0 GHz</b>	1.052	31.92
<b>1.0–2.0 GHz</b>	1.08	28.3
<b>2.0–2.5 GHz</b>	1.1	26.45
<b>2.5–5.0 GHz</b>	1.433	14.99
<b>5.0–6.0 GHz</b>	1.79	11

## Mechanical Specifications

<b>Connector Retention Tensile Force</b>	889.64 N   200 lbf
<b>Connector Retention Torque</b>	1.4 N-m   12.356 in lb
<b>Coupling Nut Proof Torque</b>	50 N-m   442.537 in lb
<b>Coupling Nut Proof Torque Method</b>	IEC 61169-4:9.3.6
<b>Insertion Force</b>	199.99 N   44.96 lbf
<b>Insertion Force Method</b>	IEC 61169-4:15.2.4
<b>Interface Durability</b>	500 cycles
<b>Interface Durability Method</b>	IEC 61169-4:17
<b>Mechanical Shock Test Method</b>	IEC 60068-2-27

# SFX-ADMR

---

## Environmental Specifications

<b>Operating Temperature</b>	-57 °C to +85 °C (-70.6 °F to +185 °F)
<b>Storage Temperature</b>	-70 °C to +100 °C (-94 °F to +212 °F)
<b>Attenuation, Ambient Temperature</b>	20 °C   68 °F
<b>Average Power, Ambient Temperature</b>	40 °C   104 °F
<b>Average Power, Inner Conductor Temperature</b>	100 °C   212 °F
<b>Corrosion Test Method</b>	IEC 60068-2-11
<b>Immersion Depth</b>	1 m
<b>Immersion Test Mating</b>	Mated
<b>Immersion Test Method</b>	IEC 60529:2001, IP68
<b>Thermal Shock Test Method</b>	IEC 60068-2-14
<b>Vibration Test Method</b>	IEC 60068-2-6

## Packaging and Weights

<b>Weight, net</b>	206 g   0.454 lb
--------------------	------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

<b>Immersion Depth</b>	Immersion at specified depth for 24 hours
------------------------	---