

# SFX-ANM

---



Type N Male A Series for 1/2 in SFX-500 cable

## OBSOLETE

This product was discontinued on: December 2, 2015

## Product Classification

**Product Type** Wireless and radiating connector

## General Specifications

**Body Style** Straight

**Cable Family** SFX-500

**Inner Contact Attachment Method** Captivated

**Inner Contact Plating** Gold

**Interface** N Male

**Mounting Angle** Straight

**Outer Contact Attachment Method** Radial compression

**Outer Contact Plating** Silver

**Pressurizable** No

## Dimensions

**Width** 20.57 mm | 0.81 in

**Length** 57.91 mm | 2.28 in

**Diameter** 20.57 mm | 0.81 in

**Nominal Size** 1/2 in

## Electrical Specifications

**3rd Order IMD at Frequency** -115 dBm @ 1800 MHz

**3rd Order IMD Test Method** Two +43 dBm carriers

**Return Loss Note** Measurements taken using a .9 m (3 ft) jumper assembly

**Average Power at Frequency** 600.0 W @ 900 MHz

# SFX-ANM

---

<b>Cable Impedance</b>	50 ohm
<b>Connector Impedance</b>	50 ohm
<b>dc Test Voltage</b>	2000 V
<b>Inner Contact Resistance, maximum</b>	1 mOhm
<b>Insulation Resistance, minimum</b>	5000 MOhm
<b>Operating Frequency Band</b>	0 – 6000 MHz
<b>Outer Contact Resistance, maximum</b>	0.25 mOhm
<b>Peak Power, maximum</b>	10 kW
<b>RF Operating Voltage, maximum (vrms)</b>	707 V
<b>Shielding Effectiveness</b>	110 dB

## VSWR/Return Loss

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
<b>0.05–1.0 GHz</b>	1.05	32.26
<b>1.0–2.0 GHz</b>	1.08	28.3
<b>2.0–2.5 GHz</b>	1.1	26.45
<b>2.5–5.0 GHz</b>	1.29	18
<b>5.0–6.0 GHz</b>	1.38	16

## Mechanical Specifications

<b>Attachment Durability</b>	25 cycles
<b>Connector Retention Tensile Force</b>	889.64 N   200 lbf
<b>Connector Retention Torque</b>	1.4 N-m   12.356 in lb
<b>Coupling Nut Proof Torque</b>	1.7 N-m   15.046 in lb
<b>Coupling Nut Proof Torque Method</b>	IEC 61169-16:9.3.6
<b>Coupling Nut Retention Force</b>	449.98 N   101.16 lbf
<b>Coupling Nut Retention Force Method</b>	IEC 61169-16:9.3.11
<b>Insertion Force</b>	27.98 N   6.29 lbf
<b>Insertion Force Method</b>	IEC 61169-16:9.3.5
<b>Interface Durability</b>	500 cycles
<b>Interface Durability Method</b>	IEC 61169-16:9.5
<b>Mechanical Shock Test Method</b>	IEC 60068-2-27

# SFX-ANM

---

## Environmental Specifications

<b>Operating Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)
<b>Storage Temperature</b>	-65 °C to +100 °C (-85 °F to +212 °F)
<b>Attenuation, Ambient Temperature</b>	20 °C   68 °F
<b>Average Power, Ambient Temperature</b>	40 °C   104 °F
<b>Average Power, Inner Conductor Temperature</b>	100 °C   212 °F
<b>Corrosion Test Method</b>	IEC 60068-2-11
<b>Immersion Depth</b>	1 m
<b>Immersion Test Mating</b>	Mated
<b>Immersion Test Method</b>	IEC 60529:2001, IP68
<b>Moisture Resistance Test Method</b>	IEC 60068-2-3
<b>Thermal Shock Test Method</b>	IEC 60068-2-14
<b>Vibration Test Method</b>	IEC 60068-2-6

## Packaging and Weights

<b>Weight, net</b>	64 g   0.141 lb
--------------------	-----------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

<b>Immersion Depth</b>	Immersion at specified depth for 24 hours
------------------------	---