

AT-30-43-MF



30 dB Coaxial Attenuator DC-6000 4.3-10 M-F

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Attenuator

General Specifications

Device Type Attenuator

Application Indoor

Color Silver

Inner Contact Plating Silver

Interface 4.3-10 Male

Interface 2 4.3-10 Female

Outer Contact Plating Trimetal

Electrical Specifications

Return Loss, minimum 20.8 dB

Attenuation 30 dB

Attenuation Tolerance ± 0.8 dB

Average Power, maximum 2 W

Impedance 50 ohm

Operating Frequency Band 0 – 6000 MHz

Peak Power, maximum 0.5 kW

VSWR 1.2

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Regulatory Compliance/Certifications

AT-30-43-MF

Agency

CHINA-ROHS
REACH-SVHC
ROHS
UK-ROHS

Classification

Below maximum concentration value
Compliant as per SVHC revision on www.andrew.com/ProductCompliance
Compliant
Compliant

