

SMALL-M-CAPKIT



Male End Cap for 4.3-10 series.


Product Classification

Product Type	Wireless and radiating connector
Product Brand	HELIAX®

Dimensions

Length	23.88 mm 0.94 in
Diameter	19.81 mm 0.78 in

Outline Drawing



Mechanical Specifications

Coupling Nut Proof Torque	8 N-m 70.806 in lb
---------------------------	----------------------

SMALL-M-CAPKIT

Mechanical Shock Test Method	IEC 60068-2-27
Environmental Specifications	
Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-65 °C to +125 °C (-85 °F to +257 °F)
Attenuation, Ambient Temperature	20 °C 68 °F
Average Power, Ambient Temperature	40 °C 104 °F
Average Power, Inner Conductor Temperature	100 °C 212 °F
Corrosion Test Method	IEC 60068-2-11
Immersion Depth	1 m
Immersion Test Mating	Mated
Immersion Test Method	IEC 60529:2001, IP68
Moisture Resistance Test Method	IEC 60068-2-3
Thermal Shock Test Method	IEC 60068-2-14
Vibration Test Method	IEC 60068-2-6

Packaging and Weights

Weight, net	26.7 g 0.059 lb
-------------	-------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Immersion Depth	Immersion at specified depth for 24 hours
-----------------	---