

CBC7821-DF-19F-KIT

Triplexer 19" Tray Kit, 6 CBC7821-DF in a 19" tray with antenna port in front

OBSOLETE

This product was discontinued on: December 1, 2019

Replaced By:

CBC7823T-DS-43 Twin Triplexer 700/850/1695-2360,dc Sense, 4.3-10
E14F60P04

Product Classification

Product Type Triplexer

General Specifications


Product Family CBC7821
Color Gray
Common Port Label COMM
Modularity 6-Hex
Mounting Rack
RF Connector Interface 7-16 DIN Female
RF Connector Interface Body Style Medium neck

Dimensions

Height 221.5 mm | 8.72 in
Width 482 mm | 18.976 in
Depth 200 mm | 7.874 in
Ground Screw Diameter 6.35 mm | 0.25 in

CBC7821-DF-19F-KIT

Outline Drawing



Electrical Specifications

Impedance	50 ohm
License Band, Band Pass	AWS 1700 CEL 850 DCS 1800 IMT 2100 PCS 1900 USA 700 USA 750

Electrical Specifications, Common Port

Composite Power, RMS	500 W
-----------------------------	-------

Electrical Specifications, dc Power/Alarm

dc/AISG Pass-through, combiner	Branch 1 Branch 2 Branch 3
dc/AISG Pass-through, demultiplexer	Branch 1 Branch 2 Branch 3

CBC7821-DF-19F-KIT

Lightning Surge Current	10 kA
Lightning Surge Current Waveform	8/20 waveform


Electrical Specifications

Sub-module	1 2 3 4 5 6	1 2 3 4 5 6	1 2 3 4 5 6
Branch	1	2	3
Port Designation	698-787	824-894	1710-2170
License Band	USA 700, Band Pass USA 750, Band Pass	CEL 850, Band Pass	AWS 1700, Band Pass DCS 1800, Band Pass IMT 2100, Band Pass PCS 1900, Band Pass

Electrical Specifications, Band Pass

Frequency Range, MHz	698–787	824–894	1710–2170
Insertion Loss, typical, dB	0.2	0.2	0.15
Total Group Delay, maximum, ns	30	30	6
Return Loss, minimum, dB	22	22	22
Return Loss, typical, dB	24	24	24
Isolation, minimum, dB	50	50	50
3rd Order PIM, typical, dBc	-153	-153	-153
3rd Order PIM Test Method	2 x 20 W CW tones	2 x 20 W CW tones	2 x 20 W CW tones

Block Diagram



Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
-----------------------	--------------------------------------

CBC7821-DF-19F-KIT

Relative Humidity	5%–100%
Corrosion Test Method	IEC 60068-2-11, 30 days
Ingress Protection Test Method	IEC 60529:2001, IP67

Packaging and Weights

Included	Mounting hardware
Volume	21.3 L
Weight, net	24.5 kg 54.013 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

