## CBC1726-DL-2X | E11F02P51



Twin Diplexer, 1800-2100//2300-2600 MHz, dc bypass on 1800-2100 ports

#### OBSOLETE

This product was discontinued on: December 30, 2024Replaced By:E14F06P48Twin Diplexer, 1350-2200 / 2300-2700 MHz, dc bypass all ports, 4.3-10 connectors


### Product Classification

Product Type	Diplexer	
General Specifications		
Product Family	CBC1726	
Color	Gray	
Common Port Label	COMM	
Modularity	2-Twin	
Mounting	Pole   Wall	
Mounting Pipe Hardware	Band clamps (2)	
RF Connector Interface	7-16 DIN Female	
RF Connector Interface Body Style	Medium neck	
Dimensions		
Height	152.4 mm   6 in	
Width	123 mm   4.843 in	
Depth	121 mm   4.764 in	
Ground Screw Diameter	6 mm   0.236 in	
Mounting Pipe Diameter Range	42.6-122 mm	

### Outline Drawing

Page 1 of 4





### **Electrical Specifications**

Impedance

50 ohm

### Electrical Specifications, dc Power/Alarm

dc/AISG Pass-through, combiner	Branch 1
dc/AISG Pass-through, demultiplexer	Branch 1
Lightning Surge Current	3 kA
Lightning Surge Current Waveform	10/350 waveform

### **Electrical Specifications**

Sub-module	1   2	1   2
Branch	1	2

Page 2 of 4




# CBC1726-DL-2X | E11F02P51

Port Designation	1710-2170	2300-2690
License Band	AWS 1700, Band Pass DCS 1800, Band Pass IMT 2100, Band Pass PCS 1900, Band Pass TDD 1900, Band Pass TDD 2000, Band Pass	IMT 2600, Band Pass WCS 2300, Band Pass TDD 2300, Band Pass TDD 2600, Band Pass

### Electrical Specifications, Band Pass

Frequency Range, MHz	1710-2170	2300-2690
Insertion Loss, maximum, dB	0.4	0.4
Insertion Loss, typical, dB	0.3	0.35
Total Group Delay, maximum, ns	30	30
Return Loss, minimum, dB	18	18
Return Loss, typical, dB	20	20
Isolation, minimum, dB	50	50
Input Power, PEP, maximum, W	3500	3500
3rd Order PIM, typical, dBc	-155	-155
3rd Order PIM Test Method	2 x 20 W CW tones	2 x 20 W CW tones

### Block Diagram



#### **Environmental Specifications**

**Operating Temperature** 

**Relative Humidity** 

-40 °C to +60 °C (-40 °F to +140 °F)

Up to 100%

Page 3 of 4



### CBC1726-DL-2X | E11F02P51

#### **Corrosion Test Method**

Ingress Protection Test Method

IEC 60068-2-11, 30 days IEC 60529:2001, IP67

### Packaging and Weights

Included Volume Weight, net Mounting hardware 2.3 L 5 kg | 11.023 lb

Page 4 of 4

