## 760250075 | C-036-LA-5K-M12BK/25G/GY/FS



Fiber indoor/outdoor cable, LazrSPEED®, Single Jacket/Single Armor, 90 min Fire Survival, Low Smoke Zero Halogen (LSZH), 36 fiber, Multimode OM4, Gel-Filled, Stranded Loose Tube, Black jacket color, Meters cable marking

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

**Product Series** C-LA

### General Specifications

Armor Type Corrugated steel

Cable Type Stranded loose tube

Construction TypeArmoredSubunit TypeGel-filled

Filler, quantity 3

Jacket Color Black

Jacket Marking Method Inkjet

Jacket Marking Text COMMSCOPE GB OPTICAL CABLE 760250075 36x50/125 0M4 ULSZH [Serial number]

[metre mark]

Subunit, quantity3Fibers per Subunit, quantity12Total Fiber Count36


**Dimensions** 

Buffer Tube/Subunit Diameter 2.5 mm | 0.098 in Diameter Over Jacket 14 mm | 0.551 in



# 760250075 | C-036-LA-5K-M12BK/25G/GY/FS

### Representative Image



### Mechanical Specifications

Minimum Bend Radius, loaded330 mm | 12.992 inMinimum Bend Radius, unloaded200 mm | 7.874 inTensile Load, long term, maximum1200 N | 269.771 lbfTensile Load, short term, maximum4000 N | 899.236 lbfCompression20 N/mm | 114.203 lb/in

Compression Test Method IEC 60794-1 E3

**Impact** 5 N-m | 44.254 in lb

Impact Test Method IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method IEC 60794-1 E1

**Twist** 5 cycles

Twist Test Method IEC 60794-1 E7

Optical Specifications

**Fiber Type** OM4 | OM4, LazrSPEED®

## **Environmental Specifications**

Operating Temperature  $-30 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-22  $^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Page 2 of 3



# 760250075 | C-036-LA-5K-M12BK/25G/GY/FS

**Cable Qualification Standards** EN 187105 | IEC 60794-1-2

**Environmental Space** Aerial, lashed | Buried | Low Smoke Zero Halogen (LSZH)

Flame Test Method | IEC 60331-25 | IEC 60332-1 | IEC 60332-3-24 | IEC 60754-1 | IEC 60754-

2 | IEC 61034-2 | NES 713 (<=5 - jacket material only)

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method IEC 60794-1 F5

**Environmental Test Specifications** 

**Low High Bend Test Method** IEC 60794-1 E11

**Temperature Cycle** -20 °C to +70 °C (-4 °F to +158 °F)

**Temperature Cycle Test Method** IEC 60794-1 F1

Packaging and Weights

**Cable weight** 240 kg/km | 161.273 lb/kft

Included Products

CS-5K-LT – LazrSPEED® 550 OM4 Bend-Insensitive Multimode

Fiber

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

