#### Base Product



0.9m | 3 ft Sentinel® High Performance Antenna, dual-polarized, 24.250 – 26.500 GHz


| Product Classification                           |  |  |
|--|--|--|
| Product Type                                     | Microwave antenna  |  |
| Product Brand                                    | Sentinel®  |  |
| General Specifications                           |  |  |
| Antenna Type                                     | SHPX - Sentinel® High Performance Antenna, dual-<br>polarized                              |  |
| Polarization                                     | Dual   |  |
| Side Struts, Included                            | 0  |  |
| Side Struts, Optional                            | 1  |  |
| Dimensions                                       |  |  |
| Diameter, nominal                                | 0.9 m   3 ft   |  |
| Electrical Specifications                        |  |  |
| Operating Frequency Band                         | 24.250 – 26.500 GHz  |  |
| Gain, Low Band                                   | 45.6 dBi   |  |
| Gain, Mid Band                                   | 45.8 dBi   |  |
| Gain, Top Band                                   | 46.2 dBi   |  |
| Boresite Cross Polarization Discrimination (XPD) | 30 dB  |  |
| Front-to-Back Ratio                              | 77 dB  |  |
| Beamwidth, Horizontal                            | 0.8 °  |  |
| Return Loss                                      | 17.7 dB  |  |
| VSWR   | 1.3  |  |
| Radiation Pattern Envelope Reference (RPE)       | 7304B  |  |
| Electrical Compliance                            | Brazil Anatel Class 2   Canada SRSP<br>324.25   ETSI 302 217 Class 4   US FCC Part<br>101A |  |

Page 1 of 6



| Cross Polarization Discrimination (XPD) Electrical Compliance | ETSI EN 302217 XPD Category 3 |
|---|-------------------------------|
| Mechanical Specifications                                     |                               |
| Compatible Mounting Pipe Diameter                             | 90 mm-120 mm   3.5 in-4.7 in  |
| Fine Azimuth Adjustment Range                                 | ±15°                          |
| Fine Elevation Adjustment Range                               | ±15°                          |
| Wind Speed, operational                                       | 180 km/h   111.847 mph        |
| Wind Speed, survival  | 250 km/h   155.343 mph        |
|   |                               |

## Antenna Dimensions and Mounting Information



| Dimensions in inches (mm) |            |          |            |           |            |
|---------------------------|------------|----------|------------|-----------|------------|
| Antenna Size, ft (m)      | А          | В        | С          | D         | E          |
| 3 (0.9)                   | 38.9 (987) | 16 (407) | 33.7 (855) | 7.2 (183) | 34.9 (887) |

### Wind Forces at Wind Velocity Survival Rating

Axial Force (FA)

Angle  $\alpha$  for MT Max

Side Force (FS)

Twisting Moment (MT)

Zcg without Ice

3353 N | 753.785 lbf 30° 1680 N | 377.679 lbf 1605 N-m | 14,205.447 in lb 310 mm | 12.205 in

Page 2 of 6




SHPX3-26/B

Zcg with 1/2 in (12 mm) Radial Ice Weight with 1/2 in (12 mm) Radial Ice 388 mm | 15.276 in 87 kg | 191.802 lb

Page 3 of 6



Wind Forces at Wind Velocity Survival Rating Image



Mτ

## Packaging and Weights

#### Weight, net

24 kg | 52.911 lb

## Regulatory Compliance/Certifications

Classification

#### Agency

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

### \* Footnotes

#### **Operating Frequency Band**

Bands correspond with CCIR recommendations or common allocations used throughout the world. Other ranges can be accommodated on special order.

Page 4 of 6



| Gain, Mid Band  | For a given frequency band, gain is primarily a function of<br>antenna size. The gain of Andrew antennas is determined by<br>either gain by comparison or by computer integration of the<br>measured antenna patterns.  |
|---|---|
| Boresite Cross Polarization Discrimination (XPD)              | The difference between the peak of the co-polarized main<br>beam and the maximum cross-polarized signal over an angle<br>twice the 3 dB beamwidth of the co-polarized main beam.  |
| Front-to-Back Ratio   | Denotes highest radiation relative to the main beam, at 180° ±40°, across the band. Production antennas do not exceed rated values by more than 2 dB unless stated otherwise.   |
| Return Loss   | The figure that indicates the proportion of radio waves incident upon the antenna that are rejected as a ratio of those that are accepted.  |
| VSWR  | Maximum; is the guaranteed Peak Voltage-Standing-Wave-<br>Ratio within the operating band.  |
| Radiation Pattern Envelope Reference (RPE)                    | Radiation patterns define an antenna's ability to discriminate<br>against unwanted signals. Under still dry conditions,<br>production antennas will not have any peak exceeding the<br>current RPE by more than 3dB, maintaining an angular<br>accuracy of +/-1° throughout |
| Cross Polarization Discrimination (XPD) Electrical Compliance | The difference between the peak of the co-polarized main<br>beam and the maximum cross-polarized signal over an angle<br>twice the 3 dB beamwidth of the co-polarized main beam.  |
| Wind Speed, operational                                       | For VHLP(X), SHP(X), HX and USX antennas, the wind speed<br>where the maximum antenna deflection is 0.3 x the 3 dB<br>beam width of the antenna. For other antennas, it is defined<br>as a deflection is equal to or less than 0.1 degrees.                                 |
| Wind Speed, survival  | The maximum wind speed the antenna, including mounts<br>and radomes, where applicable, will withstand without<br>permanent deformation. Realignment may be required. This<br>wind speed is applicable to antenna with the specified<br>amount of radial ice.                |
| Axial Force (FA)  | Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.                                   |
| Side Force (FS)   | Maximum side force exerted on the mounting pipe as a result of wind from the most critical direction for this   |

Page 5 of 6



#### **Twisting Moment (MT)**

parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

Page 6 of 6

