

H-4X4-CPUSE-DAI6

Low PIM 4x4 High Power Hybrid Matrix, 555–2 700 MHz



Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Hybrid matrix

General Specifications

Device Type Hybrid
Application Indoor/Outdoor
Color Silver
Inner Contact Plating Silver
Interface 7-16 DIN Female
Outer Contact Plating Trimetal

Dimensions

Height 34 mm | 1.339 in
Width 191 mm | 7.52 in
Length 191 mm | 7.52 in

Electrical Specifications

3rd Order IMD -160 dBc
3rd Order IMD Test Method Two +43 dBm carriers
Insertion Loss at Frequency Band 0.3 dB @ 555–2700 MHz
Return Loss, minimum 20.8 dB
Average Power, maximum 100 W
Coupling 6.1 dB
Coupling Tolerance ±1.0dB @ 698–2700 MHz | ±2.5dB @ 555–698 MHz
Impedance 50 ohm

H-4X4-CPUSE-DAI6

Isolation at Frequency Band	25 dB @ 555–2700 MHz
Operating Frequency Band	555 – 2700 MHz
Peak Power, maximum	1 kW
Reflected Power, maximum	100 W
VSWR	1.2

Mechanical Specifications

Coupling Nut Proof Torque	25 N-m 221.269 in lb
----------------------------------	------------------------

Environmental Specifications

Operating Temperature	-35 °C to +85 °C (-31 °F to +185 °F)
Relative Humidity	Up to 100%
Ingress Protection Test Method	IEC 60529:2001, IP65

Packaging and Weights

Height, packed	45 mm 1.772 in
Width, packed	210 mm 8.268 in
Length, packed	210 mm 8.268 in
Weight, gross	2.3 kg 5.071 lb
Weight, net	1.8 kg 3.968 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

