


43211A



Butterfly Hanger for 1/2 in or 3/8 in coaxial cable and elliptical waveguide 180, 220, and 240

Product Classification

Product Type	Hanger kit
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	1
Color	Silver
Hanger Type	Standard butterfly hanger
Mounting	3/8 in (M10) drilled cable ladder

Dimensions

Maximum Stack Height	0
Height	31.8 mm 1.252 in
Width	38.1 mm 1.5 in
Length	40.6 mm 1.598 in
Compatible Cable Diameter Range	9–12 mm
Compatible Diameter, maximum	16.3 mm 0.642 in
Compatible Diameter, minimum	10.4 mm 0.409 in
Nominal Size	1/2 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

43211A

Material Type Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Double cable weight

Packaging and Weights

Height, packed 14.8 cm | 5.827 in

Width, packed 10.6 cm | 4.173 in

Length, packed 9 cm | 3.543 in

Packaging quantity 10

Weight, gross 0.34 kg | 0.75 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power