

BHS-114



Single Block Hanger for 1-1/4 in coaxial cable

Product Classification

Product Type	Hanger kit
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	1
Color	Black
Hanger Type	Single block hanger
Mounting	3/8 in (M10) drilled cable ladder

Dimensions

Maximum Stack Height	4
Height	51.1 mm 2.012 in
Width	59.9 mm 2.358 in
Length	67.1 mm 2.642 in
Compatible Cable Diameter Range	39.6–40.6 mm
Compatible Diameter, maximum	40.6 mm 1.598 in
Compatible Diameter, minimum	39.6 mm 1.559 in
Nominal Size	1-1/4 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

BHS-114

Material Type Engineered plastic

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 5.1 cm | 2.008 in

Width, packed 17.8 cm | 7.008 in

Length, packed 25.4 cm | 10 in

Packaging quantity 10

Weight, gross 0.86 kg | 1.896 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power