

CPCFSX2

Base Product



GigaSPEED X10D® VisiPatch® 360 to 360GS10E 4 Pair Solid Hybrid Patch Cord

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Twisted pair patch cord
Product Brand	GigaSPEED X10D® VisiPatch 360®
Product Series	CPC
Ordering Note	Cords < 2 m are valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords Cords > 2 m are authorized for use in channels and are an effective standalone method used to connect active devices

General Specifications

ANSI/TIA Category	6A
Cable Type	U/UTP (unshielded)
Conductor Type	Solid
Interface, Connector A	VisiPatch® 360
Interface Feature, connector A	Standard
Interface, Connector B	RJ45 plug
Interface Feature, connector B	Standard
Jacket Color	Black Blue Dark gray Light blue Lilac Orange Red Slate Spring green White Yellow
Pairs, quantity	4
Transmission Standards	IEEE 802.3bt Type 4
Wiring	T568B

Dimensions

Cable Assembly Length Range (m)	2 – 30
---------------------------------	--------

CPCFSX2

Cable Assembly Length Range (ft)	7 – 100
Diameter Over Jacket	7.24 mm 0.285 in
Compatible Conductor Gauge, solid	24 AWG

Wiring Diagram

	Connector A	Connector B
Position 1	Blue	White/Orange
Position 2	Lt. Blue	Orange
Position 3	Orange	Lt. Green
Position 4	White/Orange	Blue
Position 5	Green	Lt. Blue
Position 6	Lt. Green	Green
Position 7	Brown	Lt. Brown
Position 8	Lt. Brown	Brown

Electrical Specifications

dc Resistance, maximum	0.3 ohm
------------------------	---------

Ordering Tree

CPC-

9

10

11

12

0

1

F

0

5

0

Outlet Color	
9	0 Not applicable
	1 Black
	2 Blue
	3 Gray
	4 Green
	5 Ivory
	6 Orange
	7 Red
	8 White
	9 Yellow
	B Lilac

Jacket Color	
10	1 Black
	2 Light blue
	3 Dark gray
	4 Spring green
	5 Ivory
	6 Orange
	7 Red
	8 White
	9 Yellow
	B Lilac
11	C Gray
	K Pink
	L Violet
	M Green
	Z Blue

UOM		
11	F	Foot
	M	Meter
	N	Inch
	C	Centimeter

Length

12

XXX

- Notes
- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
 - Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

CPCFSX2

Material Specifications

Contact Plating Material	Precious metals
Material Type	Copper alloy Polycarbonate

Mechanical Specifications

Plug Insertion Life, minimum	200 times
Plug Retention Force, minimum	44 N 9.892 lbf

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Safety Standard	ETL cETL

Packaging and Weights

Packaging quantity	1
--------------------	---

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system