

# L5CLICKB

---



Double Click-on Hanger for 7/8 in coaxial cable - Hardware Sold Separately (search 243095-SERIES-HARDWARE for options available)

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Cables per Hanger</b>	2
<b>Color</b>	Black
<b>Hanger Type</b>	Click-on hanger
<b>Mounting</b>	3/8 in (M10) drilled cable ladder

## Dimensions

<b>Maximum Stack Height</b>	4
<b>Height</b>	51.1 mm   2.012 in
<b>Width</b>	56.9 mm   2.24 in
<b>Length</b>	111 mm   4.37 in
<b>Compatible Cable Diameter Range</b>	27.7–28.2 mm
<b>Compatible Diameter, maximum</b>	28.2 mm   1.11 in
<b>Compatible Diameter, minimum</b>	27.5 mm   1.083 in
<b>Nominal Size</b>	7/8 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

# L5CLICKB

---

**Material Type** Engineered plastic

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Environmental Strength Capability** Double cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

**Height, packed** 24.4 cm | 9.606 in

**Width, packed** 13.4 cm | 5.276 in

**Length, packed** 11.5 cm | 4.528 in

**Packaging quantity** 10

**Weight, gross** 0.98 kg | 2.161 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power