


# 5-1427071-6 | CS30CM BLU C6 4/24 U/UTP RIB 305M

---



Copper Cable, category 6, 4 pair, UTP, CM rated, 24 AWG, 305 m reel in box, blue

## Product Classification

<b>Regional Availability</b>	Asia
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Twisted pair cable

## General Specifications

<b>Product Number</b>	CS30CM
<b>ANSI/TIA Category</b>	6
<b>Cable Component Type</b>	Horizontal
<b>Cable Type</b>	U/UTP (unshielded)
<b>Conductor Type, singles</b>	Solid
<b>Conductors, quantity</b>	8
<b>Jacket Color</b>	Blue
<b>Pairs, quantity</b>	4
<b>Transmission Standards</b>	ABNT/NBR 14703   ANSI/TIA-568.2-D   Anatel   CENELEC EN 50288-6-1   ISO/IEC 11801 Class E

## Dimensions

<b>Cable Length</b>	304.8 m   1000 ft
<b>Diameter Over Insulated Conductor</b>	0.978 mm   0.038 in
<b>Diameter Over Jacket, nominal</b>	5.588 mm   0.22 in
<b>Conductor Gauge, singles</b>	24 AWG

## Electrical Specifications

<b>Characteristic Impedance</b>	100 ohm
<b>dc Resistance Unbalance, maximum</b>	5 %
<b>dc Resistance, maximum</b>	9.38 ohms/100 m   2.859 ohms/100 ft
<b>Delay Skew, maximum</b>	45 ns

# 5-1427071-6 | CS30CM BLU C6 4/24 U/UTP RIB 305M

<b>Dielectric Strength, minimum</b>	1500 Vac   2500 Vdc
<b>Mutual Capacitance at Frequency</b>	5.6 nF/100 m @ 1 kHz
<b>Nominal Velocity of Propagation (NVP)</b>	68 %
<b>Operating Frequency, maximum</b>	250 MHz
<b>Operating Voltage, maximum</b>	80 V
<b>Propagation Delay, maximum</b>	536 ns/100m @250MHz
<b>Remote Powering</b>	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

## Electrical Cable Performance

<b>CS</b>	CommScope	<b>NEXT</b>	Near End Crosstalk (dB/100m)
<b>STD</b>	Refers to the standard value listed under Transmission Standards in the Electrical Specifications above	<b>PSNEXT</b>	Power Sum Near End Crosstalk (db/100m)
<b>TYP</b>	Typical Electrical Performance	<b>ACRF</b>	Attenuation to Crosstalk Ratio - Far End (dB/100m)
<b>IL</b>	Insertion Loss (dB/100m)	<b>RL</b>	Return Loss (dB)
<b>ACR</b>	Attenuation to Crosstalk Ratio (dB/100m)	<b>ELTCTL</b>	Equal Level Transverse Conversion Transfer Loss (dB/100m)
<b>PSACR</b>	Power Sum Attenuation to Crosstalk Ratio (dB/100m)		
<b>PSACRF</b>	Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)		
<b>TCL</b>	Transverse Conversion Loss (dB/100m)		

Freq. MHz	IL	NEXT	ACR	PSNEXT	PSACR	ACRF	PSACRF	RL	TCL	ELTCTL
	STD	STD	STD	STD	STD	STD	STD	STD	STD	STD
1	2	74.3	72.3	72.3	70.3	67.8	64.8	20	40	35
4	3.8	65.3	61.5	63.3	59.5	55.8	52.8	23	40	23
8	5.3	60.8	55.4	58.8	53.4	49.9	46.9	24.5	40	16.9
10	6	59.3	53.3	57.3	51.3	47.8	44.8	25	40	15
16	7.6	56.2	48.7	54.2	46.7	43.7	40.7	25	38	10.9
20	8.5	54.8	46.3	52.8	44.3	41.8	38.8	25	37	9
25	9.5	53.3	43.8	51.3	41.8	39.8	36.8	24.3	36	7
31.25	10.7	51.9	41.2	49.9	39.2	37.9	34.9	23.6	35.1	
62.5	15.4	47.4	32	45.4	30	31.9	28.9	21.5	32	
100	19.8	44.3	24.5	42.3	22.5	27.8	24.8	20.1	30	
155	25.2	41.4	16.3	39.4	14.3	24	21	18.8	28.1	
200	29	39.8	10.8	37.8	8.8	21.8	18.8	18	27	
250	32.8	38.3	5.5	36.3	3.5	19.8	16.8	17.3	26	

## Material Specifications

<b>Conductor Material</b>	Bare copper
<b>Insulation Material</b>	Polyolefin
<b>Jacket Material</b>	PVC

## Mechanical Specifications

<b>Minimum Bend Radius Note</b>	4 times the outer cable diameter
---------------------------------	----------------------------------

## Environmental Specifications

<b>Installation temperature</b>	0 °C to +60 °C (-32 °F to +140 °F)
<b>Operating Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Storage Temperature</b>	-20 °C to +80 °C (-4 °F to +176 °F)
<b>Environmental Space</b>	Non-plenum
<b>Flame Test Method</b>	ABNT/NBR 14705   CM

## Packaging and Weights

<b>Cable weight</b>	33.335 kg/km   22.4 lb/kft
<b>Packaging Type</b>	Reel in box

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

