MT-216-NS



Cellular Pipe Frame, 12 ft face

Product Classification

Product Type

Pipe mount

General Specifications

Mounting	Pipe, 114.3 mm (4-1/2 in) OD
	· · · [• •, · · · · • · · · · · · (· · ·, = · · ·) • =

Dimensions


Height	254 mm 10 in
Face Width	3.81 m 12.5 ft
Width	3810 mm 150 in
Length	88.9 mm 3.5 in

Page 1 of 3



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

Outline Drawing



Material Specifications

Material Type

Hot dip galvanized steel

Mechanical Specifications

Wind Rating120 mph (BWS) at 150 ft AGL | 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBCWind Rating CriteriaFour 72 in x 8 in panel antennas per sectorWind Rating Test MethodTIA/EIA-222

Packaging and Weights

Included	Cellular pipe frames
Packaging quantity	1
Weight, net	66.3 kg 146.166 lb

Regulatory Compliance/Certifications

Page 2 of 3



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

MT-216-NS

Agency

Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system ROHS Compliant/Exempted	CHINA-ROHS	Above maximum concentration value
	ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
	ROHS	Compliant/Exempted
UK-ROHS Compliant/Exempted	UK-ROHS	Compliant/Exempted



* Footnotes

Wind Rating

BWS-Base Wind Speed; FBC-Florida Building Code

Page 3 of 3

