

16-port sector antenna, 4x 694-960, 4x 1427-2690, and 8x 1695-2690 MHz 65° HPBW, 8 x RET

- All Internal RET actuators are connected in "Cascaded SRET" configuration
- Retractable tilt indicator rods
- Antenna shape optimized for wind load reduction

### General Specifications

Antenna Type Sector

Band Multiband

**Grounding Type**RF connector inner conductor and body grounded to reflector and mounting

bracket

Performance NoteOutdoor usageRF Connector Interface4.3-10 Female

**RF Connector Location** Bottom

RF Connector Quantity, high band 0
RF Connector Quantity, mid band 12
RF Connector Quantity, low band 4
RF Connector Quantity, total 16

#### Remote Electrical Tilt (RET) Information

**RET Hardware** CommRET v2

**RET Interface** 8-pin DIN Female | 8-pin DIN Male

**RET Interface, quantity** 2 female | 2 male

Input Voltage 10-30 Vdc

Internal RET Low band (2) | Mid band (6)

Power Consumption, active state, maximum 8 WPower Consumption, idle state, maximum 1 W

**Protocol** 3GPP/AISG 2.0 (Single RET)

**Dimensions** 

 Width
 430 mm | 16.929 in

 Depth
 197 mm | 7.756 in




Length

2769 mm | 109.016 in

Net Weight, antenna only

44.6 kg | 98.326 lb


### Array Layout



Array ID	Frequency (MHz)	RF Connector	RET (SRET)	AISG RET UID
R1	694-960	1 - 2	1	CPxxxxxxxxxxxxxR1
R2	694-960	3 - 4	2	CPxxxxxxxxxxxxxxxR2
Y1	1695-2690	5 - 6	3	CPxxxxxxxxxxxxY1
Y2	1695-2690	7 - 8	4	CPxxxxxxxxxxxxY2
Y3	1427-2690	9 - 10	5	CPxxxxxxxxxxxxxY3
Y4	1427-2690	11 - 12	6	CPxxxxxxxxxxxxY4
Y5	1695-2690	13 - 14	7	CPxxxxxxxxxxxxxY5
Y6	1695-2690	15 - 16	8	CPxxxxxxxxxxxxY6

(Sizes of colored boxes are not true depictions of array sizes)

### Port Configuration



### **Electrical Specifications**

**Impedance** 50 ohm

**Operating Frequency Band** 1427 – 2690 MHz | 1695 – 2690 MHz | 694 – 960 MHz

Polarization ±45°

**Total Input Power, maximum** 1,200 W @ 50 °C

### **Electrical Specifications**

	R1,R2	R1,R2	R1,R2	Y3,Y4	Y3,Y4	Y3,Y4	Y3,Y4	Y3,Y4
Frequency Band, MHz	698-806	790-894	890-960	1427-1518	1695-1995	5 1920-2300	2300-250	0 2490-2690
RF Port	1-4	1-4	1-4	9-12	9-12	9-12	9-12	9-12
Gain at Mid Tilt, dBi	15.5	16.1	16.4	15.4	16.2	17.3	18.2	18.3
Beamwidth, Horizontal, degrees	61	55	53	64	68	68	61	58
Beamwidth, Vertical, degrees	7.7	6.9	6.4	6.9	5.7	5.1	4.5	4.3
Beam Tilt, degrees	2-12	2-12	2-12	2-12	2-12	2-12	2-12	2-12
USLS (First Lobe), dB	15	15	16	17	16	17	18	18
Front-to-Back Ratio at 180°, dB	35	35	32	32	32	32	32	33
Front-to-Back Total Power at 180° ± 30°, dB	23	23	23	24	26	26	27	27
Isolation, Cross Polarization, dB	27	27	27	26	26	26	26	26
Isolation, Inter-band, dB	27	27	27	26	26	26	26	26
VSWR   Return loss, dB	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153	-153	-153	-153	-153
Input Power per Port at 50°C, maximum, watts	300	300	300	250	250	250	200	200

### **Electrical Specifications**

#### Y1,Y2,Y5,Y6Y1,Y2,Y5,Y6Y1,Y2,Y5,Y6Y1,Y2,Y5,Y6

Frequency Band, MHz	1695-1995	1920-2300	2300-2500	2490-2690
RF Port	5-8,13-16	5-8,13-16	5-8,13-16	5-8,13-16
Gain at Mid Tilt, dBi	16.1	17.2	17.9	17.7
Beamwidth, Horizontal, degrees	69	64	62	61
Beamwidth, Vertical, degrees	6.4	5.6	5	4.8



Beam Tilt, degrees	2-12	2-12	2-12	2-12
USLS (First Lobe), dB	15	15	16	17
Front-to-Back Ratio at 180°, dB	32	31	32	33
Front-to-Back Total Power at 180° ± 30°, dB	26	25	26	26
Isolation, Cross Polarization, dB	27	27	27	27
Isolation, Inter-band, dB	27	27	27	27
VSWR   Return loss, dB	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153
Input Power per Port at 50°C, maximum, watts	250	250	200	200

#### Mechanical Specifications

 Wind Loading @ Velocity, frontal
 680.0 N @ 150 km/h (152.9 lbf @ 150 km/h)

 Wind Loading @ Velocity, lateral
 347.0 N @ 150 km/h (78.0 lbf @ 150 km/h)

 Wind Loading @ Velocity, maximum
 1,020.0 N @ 150 km/h (229.3 lbf @ 150 km/h)

 Wind Loading @ Velocity, rear
 434.0 N @ 150 km/h (97.6 lbf @ 150 km/h)

 Wind Speed, maximum
 241 km/h (150 mph)

### Packaging and Weights

 Width, packed
 511 mm | 20.118 in

 Depth, packed
 318 mm | 12.52 in

 Length, packed
 2890 mm | 113.78 in

 Weight, gross
 64.3 kg | 141.757 lb

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



#### Included Products

BSAMNT-4 – Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members.

Kit contains one scissor top bracket set and one bottom bracket set.

BSAMNT-M4 – Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round

members. Kit contains one scissor bracket set.

#### \* Footnotes

**Performance Note** Severe environmental conditions may degrade optimum performance

