760251048 | EPX-4U-MOD-ENC



EPX 4U sliding panel, accepts (16) G2 style splice cassettes, modules or adapter packs, providing up to 192 duplex LC ports

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel | Fiber patch/splice panel

Product Series EPX

General Specifications

Application Accepts sixteen G2 modular cassettes

Color Black

Intelligence Type Not iPatch® ready

Interface, front Unloaded

Module/Adapter Pack Slots, quantity 16

Rack Type EIA 19 in

Rack Units 4

Shelf MovementSlidingTotal Fibers, quantity384Total Ports, quantity0

Dimensions

 Height
 177.8 mm | 7 in

 Width
 482.6 mm | 19 in

 Depth
 412.75 mm | 16.25 in

Environmental Specifications

Safety Standard CSA 22.2 | UL 1863

Packaging and Weights

COMMSCOPE®

760251048 | EPX-4U-MOD-ENC

1

Packaging quantity

Weight, net 7.439 kg | 16.4 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

