


# E14F15P30



Single Quadplexer 1325-1880//2100//2300//2600 MHz, DC Block, with 4.3-10 connectors

- Industry leading PIM performance
- Designed for network modernization application, introduction of LTE2300 and LTE2600 on existing site
- Designed for network modernization application, introduction of LTE 4x4 MIMO
- Suitable for feeders cables reduction
- New 4.3-10 connectors for improved PIM performance and size reduction
- dc/AISG blocking on all ports

## Product Classification

**Product Type** Quadplexer

## General Specifications

**Color** Gray

**Modularity** 2-Twin

**Mounting** Pole | Wall

**Mounting Pipe Hardware** Band clamps (2)

**RF Connector Interface** 4.3-10 Female

## Dimensions

**Height** 48 mm | 1.89 in


**Width** 171 mm | 6.732 in

**Depth** 151 mm | 5.945 in

**Mounting Pipe Diameter Range** 42.6–122 mm

## Outline Drawing

# E14F15P30



## Electrical Specifications

**Impedance** 50 ohm

## Electrical Specifications, dc Power/Alarm

**Lightning Surge Current** 5 kA

**Lightning Surge Current Waveform** 8/20 waveform

## Electrical Specifications


Sub-module	1   2	1   2	1   2	1   2
<b>Branch</b>	1	2	3	4
<b>Port Designation</b>	PORT 1 1325-1880MHz	PORT 2 1920-2170MHz	PORT 3 2300-2400MHz	PORT 4 2500-2690MHz

# E14F15P30

## Electrical Specifications, Band Pass

Frequency Range, MHz	1325–1880	1920–2170	2300–2400	2500–2690
Insertion Loss, typical, dB	0.3	0.3	0.3	0.3
Return Loss, typical, dB	20	20	20	20
Isolation, typical, dB	37	37	37	37
Input Power, RMS, maximum, W	100	100	100	100
Input Power, PEP, maximum, W	1000	1000	1000	1000
3rd Order PIM, typical, dBc	-163	-163	-163	-163
3rd Order PIM Test Method	Two +43 dBm carriers	Two +43 dBm carriers	Two +43 dBm carriers	Two +43 dBm carriers

## Block Diagram



## Mechanical Specifications

**Wind Speed, maximum** 240 km/h | 149.129 mph

## Environmental Specifications

**Operating Temperature** -40 °C to +65 °C (-40 °F to +149 °F)

**Corrosion Test Method** IEC 60068-2-11, 30 days

# E14F15P30

---

<b>Environmental Test Method</b>	ETSI EN 300 019-1-4
<b>Ingress Protection Test Method</b>	IEC 60529:2001, IP67
<b>Vibration Test Method</b>	IEC 60068-2-6

## Packaging and Weights

<b>Included</b>	Mounting hardware
<b>Volume</b>	1.25 L
<b>Weight, net</b>	2.3 kg   5.071 lb
<b>Weight, without mounting hardware</b>	1.7 kg   3.748 lb