


760198994 | MPS100-P.WH



PowerSUM M-Series Modular Jack, RJ45, Cat5e Unshielded, ProWhite

- Modified outlet termination scheme to match other Systimax outlets and to align with the MGS400 and the MGS600 outlets

This product will be discontinued on: November 30, 2024

Replaced By:

760258934
MPS100-P.WH

PowerSUM M-Series Modular Jack, RJ45, Cat5e Unshielded, ProWhite

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

SYSTIMAX®

Product Type

Modular jack

Product Brand

PowerSUM

Product Series

MPS100E

General Specifications

ANSI/TIA Category

5e

Cable Type

Unshielded

Color

Pro white

Conductor Type

Solid | Stranded

Integrated Dust Cover Type

None

Mounting Note

Color matches with M-series Pro white Faceplates

Termination Type

IDC

Wiring

T568A | T568B

Dimensions

Height

20.32 mm | 0.8 in

Width

20.32 mm | 0.8 in

Depth

30.48 mm | 1.2 in

Compatible Conductor Gauge, solid

22 AWG | 24 AWG

760198994 | MPS100-P.WH

Compatible Conductor Gauge, stranded

22 AWG | 24 AWG

Electrical Specifications

Contact Resistance Variation, maximum

20 mOhm

Contact Resistance, maximum

100 mOhm

Current Rating at Temperature

1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface

1,500 Vac @ 60 Hz

Dielectric Withstand Voltage, RMS, contact-to-contact

1,000 Vac @ 60 Hz

Insulation Resistance, minimum

500 MOhm

Remote Powering

Fully supports the safe delivery of power over LAN cabling described by IEEE 802.3bt (Type 4) and complies with the unmating under electrical load requirements prescribed by IEC 60512-99-002

Material Specifications

Contact Plating Material

Precious metals

Material Type

Copper alloy | High-impact, flame retardant, thermoplastic

Termination Contact Plating

Nickel

Mechanical Specifications

Plug Insertion Life, minimum

750 times

Plug Insertion Life, test plug

IEC 60603-7 compliant plug

Plug Retention Force, minimum

133 N | 29.9 lbf

Environmental Specifications

Operating Temperature

-10 °C to +60 °C (+14 °F to +140 °F)

Storage Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity

Up to 95%, non-condensing

Flammability Rating

UL 94 V-0

Safety Standard

UL | cUL

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

Agency

CHINA-ROHS
ISO 9001:2015
REACH-SVHC
ROHS
UK-ROHS

Classification

Below maximum concentration value
Designed, manufactured and/or distributed under this quality management system
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant
Compliant

