# 760251000 | P-048-MP-5K-F16AQ



Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 48 fiber multi-unit with 16 fiber subunits, Multimode OM4, Gel-free, Feet jacket marking, Aqua jacket color

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series P-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

**Subunit Type** Gel-free

Jacket Color Aqua

Jacket Marking Feet

Subunit, quantity 3

Fibers per Subunit, quantity 16

Total Fiber Count 48

**Dimensions** 

**Buffer Tube/Subunit Diameter** 3 mm | 0.118 in

**Diameter Over Jacket** 9.1 mm | 0.358 in

Mechanical Specifications

Minimum Bend Radius, loaded 136 mm | 5.354 in

Minimum Bend Radius, unloaded 91 mm | 3.583 in

Tensile Load, long term, maximum 400 N | 89.924 lbf

Tensile Load, short term, maximum 1335 N | 300.12 lbf

COMMSC PE°

# 760251000 | P-048-MP-5K-F16AQ

**Compression** 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 500 m | 1,640.42 ft

**Optical Specifications** 

Fiber Type OM4, LazrSPEED® 550 | OM4, LazrSPEED® 550

### **Environmental Specifications**

Installation temperature  $0 \,^{\circ}\text{C}$  to +70  $^{\circ}\text{C}$  (+32  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

Operating Temperature  $0 \,^{\circ}\text{C}$  to +70  $^{\circ}\text{C}$  (+32  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to +70  $^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing

NEC OFNP (ETL) and c(ETL)

Flame Test Method

NFPA 130 | NFPA 262

# **Environmental Test Specifications**

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

 Low High Bend
 0 °C to +70 °C (+32 °F to +158 °F)

 Low High Bend Test Method
 FOTP-37 | IEC 60794-1 E11

 Temperature Cycle
 0 °C to +70 °C (+32 °F to +158 °F)

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights



# 760251000 | P-048-MP-5K-F16AQ

#### Cable weight

76 kg/km | 51.07 lb/kft

### Included Products

CS-5K-MP – LazrSPEED® 550 OM4 Bend-Insensitive Multimode

Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

