760251003 | P-128-MP-5K-F16AQ



Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 128 fiber multi-unit with 16 fiber subunits, Multimode OM4, Gel-free, Feet jacket marking, Aqua jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series P-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Aqua

Jacket Marking Feet

Subunit, quantity 8

Fibers per Subunit, quantity 16

Total Fiber Count 128

Dimensions

Buffer Tube/Subunit Diameter 3 mm | 0.118 in

Diameter Over Jacket 12.25 mm | 0.482 in

Mechanical Specifications

Minimum Bend Radius, loaded184 mm7.244 inMinimum Bend Radius, unloaded122 mm4.803 inTensile Load, long term, maximum400 N89.924 lbfTensile Load, short term, maximum1335 N300.12 lbf

Page 1 of 3



760251003 | P-128-MP-5K-F16AQ

Compression 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 265 m | 869.423 ft

Optical Specifications

Fiber Type OM4, LazrSPEED® 550 | OM4, LazrSPEED® 550

Environmental Specifications

Installation temperature0 °C to +70 °C (+32 °F to +158 °F)Operating Temperature0 °C to +70 °C (+32 °F to +158 °F)Storage Temperature-40 °C to +70 °C (-40 °F to +158 °F)

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing

NEC OFNP (ETL) and c(ETL)

Flame Test Method

NFPA 130 | NFPA 262

Environmental Test Specifications

Heat Age 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend0 °C to +70 °C (+32 °F to +158 °F)Low High Bend Test MethodFOTP-37 | IEC 60794-1 E11Temperature Cycle0 °C to +70 °C (+32 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights



760251003 | P-128-MP-5K-F16AQ

Cable weight

156 kg/km | 104.827 lb/kft

Included Products

CS-5K-MP – LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

