

# TP-G312-126

---



Universal Tripod Mount, 3-1/2 in OD x 126 in (88.9 mm OD x 3.2 m)

## Product Classification

<b>Product Type</b>	Tripod mount
<b>Ordering Note</b>	NSTD445 Compliant

## General Specifications

<b>Mounting</b>	Non-penetrating   Surfaces
<b>Pipe, quantity</b>	1

## Dimensions

<b>Height</b>	3,200.4 mm   126 in
<b>Width</b>	1524 mm   60 in
<b>Length</b>	1.524 m   5 ft
<b>Pipe Length</b>	3,200.4 mm   126 in
<b>Pipe Outer Diameter</b>	88.9 mm   3.5 in

## Material Specifications

<b>Material Type</b>	Hot dip galvanized steel
----------------------	--------------------------

## Mechanical Specifications

<b>Wind Rating</b>	85 mph (BWS) at 100 ft AGL using Exposure C per UBC
<b>Wind Rating Test Method</b>	TIA/EIA-222

## Packaging and Weights

<b>Included</b>	Mount, with or without pipe
<b>Packaging quantity</b>	1
<b>Weight, net</b>	86.2 kg   190.038 lb

## Regulatory Compliance/Certifications

# TP-G312-126

---

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

**\* Footnotes****Wind Rating**

BWS—Base Wind Speed; FBC—Florida Building Code