810009789/DB | C-012-LN-8F-M12BK/14D/AY/D



Fiber Indoor/Outdoor Cable, Low Smoke Zero Halogen, 12 fiber, Microsheath, Singlemode, G.657.A1, Gel-free, Meters jacket marking, Black jacket color, Dca flame rating

Product Classification


| Regional Availability | Asia Australia/New Zealand EMEA |
|------------------------------|--|
| Portfolio | CommScope® |
| Product Type | Fiber indoor/outdoor cable |
| Product Series | C-LN |
| General Specifications | |
| Cable Type | Stranded microsheath tube |
| Subunit Type | Gel-free |
| Filler, quantity | 5 |
| Jacket Color | Black |
| Jacket Marking | Meters |
| Jacket Marking Method | Inkjet |
| Jacket Marking Text | COMMSCOPE GB F.O. CABLE 810009789/DB 12x9/125 ITU-T G. 657A1 EN50575 CLASS D ULSZH (serial number) (metre mark) |
| Subunit, quantity | 1 |
| Fibers per Subunit, quantity | 12 |
| Total Fiber Count | 12 |
| Dimensions | |
| Cable Length | 2000 m 6,561.68 ft |
| Diameter Over Jacket | 6.1 mm 0.24 in |
| Representative Image | |

Page 1 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025



810009789/DB | C-012-LN-8F-M12BK/14D/AY/D



Mechanical Specifications

| Minimum Bend Radius, loaded | 100 mm 3.937 in |
|-----------------------------------|------------------------|
| Minimum Bend Radius, unloaded | 55 mm 2.165 in |
| Tensile Load, long term, maximum | 200 N 44.962 lbf |
| Tensile Load, short term, maximum | 700 N 157.366 lbf |
| Cable Crush Resistance, maximum | 10 N/mm 57.101 lb/in |
| Compression Test Method | IEC 60794-1-21 E3 |
| Impact | 2 N-m 17.701 in lb |
| Impact Test Method | IEC 60794-1-21 E4 |
| Strain Test Method | IEC 60794-1-21 E1 |

Optical Specifications

Fiber Type

G.657.A1

Optical Specifications, Wavelength Specific

| Attenuation, maximum | 0.25 dB/km @ 1,550 nm 0.27 dB/km @ 1,490 nm 0.27 dB/km @ 1,625 nm 0.36 dB/km @ 1,310 nm |
|----------------------|--|
| Standards Compliance | TIA-492CAAB (OS2) |
| | |

Environmental Specifications

| Operating Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
|--|--------------------------------------|
| EN50575 CPR Cable EuroClass Fire Performance | Dca |
| EN50575 CPR Cable EuroClass Smoke Rating | sla |

Page 2 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025



810009789/DB | C-012-LN-8F-M12BK/14D/AY/D

| EN50575 CPR Cable EuroClass Droplets | s Rating d2 | |
|--------------------------------------|--|--|
| EN50575 CPR Cable EuroClass Acidity | Rating a1 | |
| Environmental Space | Universal Low Smoke Zero Halogen (ULSZH) | |
| Water Penetration Test Method | IEC 60794-1 F5 | |
| Environmental Test Speci | fications | |
| Temperature Cycle | -40 °C to +70 °C (-40 °F to +158 °F) | |
| Temperature Cycle Test Method | IEC 60794-1-22 F1 | |
| Packaging and Weights | | |
| Cable weight | 38 kg/km 25.535 lb/kft | |
| Included Products | | |
| CS-8F-LT – Low N | lacrobending, Zero Water Peak, Dispersion-Unshifted Singlemode | |

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Fiber

Page 3 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025

