

FDH1204-24SE2



HELIAX® Direct-connect 6 x 12 hybrid trunk assembly; 6 pairs of 4AWG DC conductors x 12 pairs of single mode fibers

- RRU (top) breakout; 6 blunt-cut power cords (6-8AWG pairs), 24 single mode fibers in outdoor-rated tails with ODC-compatible interface
- BBU (bottom) breakout; 12-4AWG power conductors blunt cut, 24 single mode fibers within 12 DLC tails, grounding wire

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Hybrid cable assembly
Product Brand	HELIAX®
Product Series	FDH

General Specifications


Conductors, quantity	12
Construction Type	Direct breakout trunk
Interface, Connector A	ODC-LC
Interface Feature, connector A	Outdoor
Interface Body Style, connector A	Straight
Interface, Connector B	DLC
Interface Feature, connector B	Standard
Interface Body Style, connector B	Straight
Jacket Color	Black
Total Fibers, quantity	24

Dimensions

Cable Assembly Length Range (m)	10 – 130
Diameter Over Jacket	44.78 mm 1.763 in
Center Conductor Gauge	4 AWG

Ordering Tree

FDH1204-24SE2 - 10M



Mechanical Specifications

Minimum Bend Radius 523.2 mm | 20.598 in
Minimum Bend Radius, furcation 30 mm | 1.181 in

Optical Specifications

Fiber Type G.657.A2/B2
Insertion Loss, typical note Insertion loss is measured at 1310 and 1550 nm
Insertion Loss, typical 0.75

Environmental Specifications

Operating Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Packaging and Weights

FDH1204-24SE2

Cable weight

3.4 kg/m | 2.285 lb/ft

Regulatory Compliance/Certifications

Agency**Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant



* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)