

CX3799663 | 2000135WP1800TAPE 3K' COEX

ConQuest® Empty Conduit, 2 in, SDR 13.5, orange, with pull tape



Product Classification

| | |
|----------------------|---------------|
| Product Type | Empty conduit |
| Product Brand | ConQuest® |

General Specifications

| | |
|----------------------------|--|
| Color | Orange |
| Conduit Type | Non-toneable |
| Density Test Method | ASTM D792A |
| Density, maximum | 0.955 g/cm ³ 0.035 lb/in ³ |
| Density, minimum | 0.941 g/cm ³ 0.034 lb/in ³ |
| Design Standard | ASTM D3350-05 |
| Wall Type | Smooth |

Dimensions

| | |
|-----------------------------------|----------------------|
| Length | 914.4 m 3000 ft |
| Inner Diameter, nominal | 50.876 mm 2.003 in |
| Outer Diameter, nominal | 60.325 mm 2.375 in |
| Wall Thickness Designation | SDR 13.5 |
| Wall Thickness, minimum | 4.47 mm 0.176 in |
| Nominal Size | 2 in |

Material Specifications

| | |
|--------------------------------------|---------------------------------------|
| Flexural Modulus, minimum | 551.581 N/mm ² 80000 psi |
| Flexural Property Test Method | ASTM D790 |
| Hydrostatic Design Basis | Not pressure rated |

CX3799663 | 2000135WP1800TAPE 3K' COEX

| | |
|---------------------------------------|--|
| Hydrostatic Design Test Method | ASTM D2837 |
| Material Type | High density polyethylene (HDPE) Polyester |
| Melt Flow Rate Test Method | ASTM D1238 |
| Melt Flow Rate, maximum | 0.39 g/10 min |

Mechanical Specifications

| | |
|---|-------------------------------------|
| Minimum Bend Radius, unsupported | 660.4 mm 26 in |
| Tensile Property Test Method | ASTM D638 |
| Tensile Strength at yield, minimum | 20.684 N/mm ² 3000 psi |
| Breaking Strength | 816.466 kg 1800 lb |
| Pull Line Type | Tape |
| Pulling Tension, maximum | 1,170.268 kg 2580 lb |

Environmental Specifications

| | |
|--|-------------------------------------|
| Environmental Stress Crack Resistance | Failure rate of 10% within 96 hours |
| Environmental Stress Test Method | ASTM D1693, ESCR Condition B |

Packaging and Weights

| | |
|--------------------|----------------------------|
| Weight, net | 791.703 kg/km 532 lb/kft |
|--------------------|----------------------------|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |



* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance