



FST-T2 Flexible Service Terminal, 12f, 6 Port x 2 Fiber, 6 HMFOC Adapters (Jack/male/pinned), 2 fibers per adapter at drop side, Stub at feeder side, black, 200 ft/60 m

- Flexible Service Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-terminated and environmentally sealed for use in optical drop cable deployments
- Flexible structure allowing installation in constrained spaces

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Access terminal, with multi-fiber port
<b>Product Series</b>	FST-T2
<b>Minimum Order Quantity</b>	1

## General Specifications

<b>Cable Type</b>	Dielectric - Loose Tube
<b>Cable, quantity</b>	7
<b>Distribution Type</b>	6 ports
<b>Drop Port Type</b>	Hardened multi-fiber (HMFOC) adapter
<b>Drop Port, quantity</b>	6
<b>Enclosure Color</b>	Black
<b>Mounting</b>	Handhole   Pedestal
<b>Port Type</b>	Hardened multi-fiber (HMFOC) jack, male/pinned
<b>Port, quantity</b>	6
<b>Splitter, quantity</b>	0
<b>Stub Type</b>	Stub tail

## Dimensions


<b>Height</b>	112.5 mm   4.429 in
<b>Width</b>	53 mm   2.087 in
<b>Depth</b>	31 mm   1.22 in
<b>Cable Length, stub</b>	200 ft (60 m)

# 760245189 | FST-T2-0610-A0200F

**Cable Outer Diameter**

4.1 x 7.6 mm (0.16 x 0.30 in)

## Ordering Tree



## Material Specifications

**Enclosure Material Type**

Engineered plastic

## Optical Specifications

**Fiber Type**

G.657.A1/A2

**Operating Wavelength Range**

1310 – 1550 nm

**Attenuation Single Ports, maximum**

0.65 dB

**Return Loss, Connector, minimum**

65 dB

## Environmental Specifications

**Operating Temperature**

-40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity**

5%–100%, condensing

**Environmental Space**

Above ground | Below ground | Buried

**Qualification Standards**

IEC 61300, 1 m waterhead | Telcordia GR-3120-CORE | Telcordia GR-3152-CORE

**UV Resistance**

UV stabilized

## Packaging and Weights

# 760245189 | FST-T2-0610-A0200F

---

<b>Included</b>	Mounting hardware
<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Box   Carton
<b>Weight, without cable</b>	0.23 kg   0.507 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

