810009826/DB | C-001-DN-8G-M01WH/15G/V6

/D



Fiber Drop Cable, Façade, Duct and Aerial, FTTH, 4 fibers, Singlemode, G. 657.A2, Gel-filled, Meters jacket marking, White jacket color, Dca Flame Rating

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series C-DN

General Specifications

Cable Type Central loose tube | Drop | Tight buffer

Construction Type Breakout | Non-armored

Subunit Type Gel-filled
Inner Jacket Color White

Jacket Color White

Jacket Marking Method Inkjet

Jacket Marking TextCOMMSCOPE GB F.O. CABLE 810009826/DB G657A2 SM 1

FIBER CLASS D [SERIAL NUMBER] [MM/YY] [METRE MARK]

Subunit, quantity 1

Fibers per Subunit, quantity 1

Total Fiber Count 1

Dimensions

Cable Length 1,999.793 m | 6561 ft

Buffer Tube/Subunit Diameter1.5 mm | 0.059 inDiameter Over Jacket4.5 mm | 0.177 in


Representative Image



810009826/DB | C-001-DN-8G-M01WH/15G/V6

/D

Low Smoke Zero-Halogen Jacket
Water Blocking E-Glass
Ripcord
Aramid Yarn
1.5mm Gel Filled Tube
Optical Fiber



Material Specifications

Jacket Material Low Smoke Zero Halogen (LSZH)

Mechanical Specifications

Minimum Bend Radius, loaded75 mm | 2.953 inTensile Load, long term, maximum300 N | 67.443 lbfTensile Load, short term, maximum1000 N | 224.809 lbfCompression10 N/mm | 57.101 lb/in

Compression Test Method IEC 60794-1 E3

Impact 2 N-m | 17.701 in lb

Impact Test MethodIEC 60794-1 E4Strain Test MethodIEC 60794-1 E1

Twist 5 cycles

Twist Test Method IEC 60794-1 E7

Optical Specifications

Fiber Type G.657.A2, TeraSPEED®

Environmental Specifications

Installation temperature $0 \, ^{\circ}\text{C} \, \text{to} +60 \, ^{\circ}\text{C} \, (-32 \, ^{\circ}\text{F} \, \text{to} +140 \, ^{\circ}\text{F})$ Operating Temperature $-25 \, ^{\circ}\text{C} \, \text{to} +70 \, ^{\circ}\text{C} \, (-13 \, ^{\circ}\text{F} \, \text{to} +158 \, ^{\circ}\text{F})$ Storage Temperature $-40 \, ^{\circ}\text{C} \, \text{to} +70 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F} \, \text{to} +158 \, ^{\circ}\text{F})$

Page 2 of 5



810009826/DB | C-001-DN-8G-M01WH/15G/V6

/D

Cable Qualification Standards IEC 60794-1-2

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Rating\$1aEN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga1

outdoor and Low Smoke Zero Halogen

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method IEC 60794-1 F5

Environmental Test Specifications

Temperature Cycle -25 °C to +70 °C (-13 °F to +158 °F)

Temperature Cycle Test Method IEC 60794-1-22 F1

Packaging and Weights

Cable weight 26 kg/km | 17.471 lb/kft

Included Products

CS-8G-TB – Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T

G.657.A2, B2)

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



CS-8G-TB

Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G. 657.A2, B2)

Product Classification

 Portfolio
 CommScope®

 Product Type
 Optical fiber

General Specifications

Cladding Diameter 125 µm ±0.7 µm **Cladding Diameter Tolerance** 0.7 % Cladding Non-Circularity, maximum **Coating Diameter (Colored)** $249 \, \mu m$ **Coating Diameter (Uncolored)** 242 µm **Coating Diameter Tolerance (Colored)** ±13 µm **Coating Diameter Tolerance (Uncolored)** ±5 µm Coating/Cladding Concentricity Error, maximum 12 µm Core/Clad Offset, maximum 0.5 µm

Proof Tensile Stress 100,000 psi (0.69 GPa)

Dimensions

Fiber Curl, minimum 4 m | 13.123 ft

Mechanical Specifications

 Macrobending, 15 mm Ø mandrel, 1 turn
 0.50 dB @ 1,550 nm
 | 1.00 dB @ 1,625 nm

 Macrobending, 20 mm Ø mandrel, 1 turn
 0.10 dB @ 1,550 nm
 | 0.20 dB @ 1,625 nm

 Macrobending, 30 mm Ø mandrel, 10 turns
 0.03 dB @ 1,550 nm
 | 0.10 dB @ 1,625 nm

Coating Strip Force, maximum8.9 N | 2.001 lbfCoating Strip Force, minimum1.3 N | 0.292 lbf

Dynamic Fatigue Parameter, minimum 20

Optical Specifications

Cabled Cutoff Wavelength, maximum1260 nmPoint Defects, maximum0.1 dB

COMMSCOPE®

CS-8G-TB

Zero Dispersion Slope, maximum 0.092 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1324 nmZero Dispersion Wavelength, minimum1302 nm

Optical Specifications, Wavelength Specific

Attenuation, maximum 0.50 dB/km @ 1,310 nm | 0.50 dB/km @ 1,385

nm | 0.50 dB/km @ 1,550 nm

Dispersion, maximum 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285

nm to 1330 nm at 1310 nm

Index of Refraction 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550

nm

 $\textbf{Mode Field Diameter} \hspace{1.5cm} 8.6~\mu m \ @ 1,310~nm \hspace{0.2cm} | \hspace{0.2cm} 9.8~\mu m \ @ 1,550~nm$

Mode Field Diameter Tolerance $\pm 0.4 \,\mu\text{m}$ @ 1310 nm | $\pm 0.5 \,\mu\text{m}$ @ 1550 nm

Polarization Mode Dispersion Link Design Value, maximum 0.06 ps/sqrt(km)

Standards Compliance ITU-T G.657.A2 | ITU-T G.657.B2

Environmental Specifications

Heat Aging, maximum 0.05 dB/km @ 85 °C

 Temperature Dependence, maximum
 0.05 dB/km

 Temperature Humidity Cycling, maximum
 0.05 dB/km

Water Immersion, maximum 0.05 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Temperature Dependence, maximum Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

