810009885/DB | L-002-DN-8G-M01YL/AY/DU09 /D



Fiber Indoor/Outdoor Drop Cable, FTTH, 2 fibers, Singlemode, G.657.A2, Gel-free, Meters jacket marking, Yellow jacket color, Dca Flame Rating

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	CommScope®
Product Type	Fiber drop cable
Product Series	L-DN
General Specifications	
Cable Type	Drop Semi-tight buffer
Construction Type	Non-armored
Subunit Type	Gel-free
Jacket Color	Yellow
Jacket Marking	Meters
Jacket Marking Method	Inkjet
Jacket Marking Text	COMMSCOPE GB OPTICAL CABLE 810009885/DB 2xG657A2 SM LSZH EN50575 CLASS D (Serial NUMBER) (METRE MARK)
Subunit, quantity	2
Fibers per Subunit, quantity	1
Total Fiber Count	2
Dimensions	
Cable Length	2,000 m 6,561.68 ft
Buffer Tube/Subunit Diameter	0.9 mm 0.035 in
Diameter Over Jacket	4 mm 0.157 in

Representative Image

Page 1 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 2, 2025



810009885/DB | L-002-DN-8G-M01YL/AY/DU09 /D

ULSZH UV Stabilised Jacket Aramid Yarn Strength Elements GRP strength Member Buffered Fibres



Jacket Material

Mechanical Specifications

Minimum Bend Radius, unloaded	60 mm 2.362 in
Tensile Load, long term, maximum	600 N 134.885 lbf
Tensile Load, short term, maximum	1200 N 269.771 lbf
Compression	20 N/mm 114.203 lb/in
Compression Test Method	IEC 60794-1 E3
Impact	5 N-m 44.254 in lb
Impact Test Method	IEC 60794-1 E4
Strain Test Method	IEC 60794-1 E1
Twist	5 cycles
Twist Test Method	IEC 60794-1 E7
Optical Specifications	

Fiber Type

G.657.A2, TeraSPEED®

Low Smoke Zero Halogen (LSZH)

Environmental Specifications

Installation temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Operating Temperature	-30 °C to +60 °C (-22 °F to +140 °F)

Page 2 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 2, 2025



810009885/DB | L-002-DN-8G-M01YL/AY/DU09

Storage Temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Cable Qualification Standards	IEC 60794-1-2
EN50575 CPR Cable EuroClass Fire Performance	Dca
EN50575 CPR Cable EuroClass Smoke Rating	s1a
EN50575 CPR Cable EuroClass Droplets Rating	d0
EN50575 CPR Cable EuroClass Acidity Rating	al
Environmental Space	Drop Ducted Façade Indoor/Outdoor UV resistant for outdoor and Low Smoke Zero Halogen
Jacket UV Resistance	UV stabilized
Water Penetration	24 h
Water Penetration Test Method	IEC 60794-1 F5
Environmental Test Specifications	
Temperature Cycle	-30 °C to +60 °C (-22 °F to +140 °F)
Temperature Cycle Test Method	IEC 60794-1-2 F1
Packaging and Weights	
Cable weight	20 kg/km 13.439 lb/kft
CS-8G-TB – Enhanced Low Ma G.657.A2, B2)	acrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T

* Footnotes

/D

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 3 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 2, 2025

