

# CA-NFKM



Type N Female to 4.1-9.5 DIN Male Adapter

**OBSOLETE**

Replaced By:

TA-NFKM      Type N Female to 4.1-9.5 DIN Male Low-PIM Adapter

## Product Classification

**Product Type**      Adapter

## General Specifications


<b>Body Style</b>	Straight
<b>Inner Contact Plating</b>	Silver
<b>Interface</b>	4.1-9.5 DIN Male
<b>Interface 2</b>	N Female
<b>Mounting Angle</b>	Straight
<b>Outer Contact Plating</b>	Trimetal
<b>Pressurizable</b>	No

## Dimensions

<b>Width</b>	24 mm   0.945 in
<b>Length</b>	35 mm   1.378 in
<b>Diameter</b>	24 mm   0.945 in

## Outline Drawing

# CA-NFKM



## Electrical Specifications

Average Power at Frequency	600.0 W @ 900 MHz
Connector Impedance	50 ohm
dc Test Voltage	2500 V
Inner Contact Resistance, maximum	1.5 mOhm
Insulation Resistance, minimum	5000 MOhm
Operating Frequency Band	0 – 6000 MHz
Outer Contact Resistance, maximum	0.4 mOhm
Peak Power, maximum	10 kW
RF Operating Voltage, maximum (vrms)	707 V

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
0-3000 MHz	1.032	36.06
3000-6000 MHz	1.083	27.99

## Mechanical Specifications

# CA-NFKM

---

Coupling Nut Proof Torque	17 N-m   150.463 in lb
Coupling Nut Proof Torque Method	IEC 61169-4:17
Coupling Nut Retention Force	550 N   123.645 lbf
Coupling Nut Retention Force Method	IEC 61169-4:15.2.6
Insertion Force	27 N   6.07 lbf
Insertion Force Method	IEC 61169-16:9.3.5
Interface Durability	500 cycles
Interface Durability Method	IEC 61169-16:9.5   IEC 61169-4:17
Mechanical Shock Test Method	IEC 60068-2-27

## Environmental Specifications

Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-65 °C to +125 °C (-85 °F to +257 °F)
Attenuation, Ambient Temperature	20 °C   68 °F
Average Power, Ambient Temperature	40 °C   104 °F
Average Power, Inner Conductor Temperature	100 °C   212 °F
Climatic Sequence Test Method	IEC 60068-1
Corrosion Test Method	IEC 60068-2-11
Damp Heat Steady State Test Method	IEC 60068-2-3
Thermal Shock Test Method	IEC 60068-2-14
Vibration Test Method	IEC 60068-2-6

## Packaging and Weights

Weight, net	50.33 g   0.111 lb
-------------	--------------------

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system