## L2HM-D



Product Classification

#### 4.3-10 Male for 3/8 in LDF2-50 cable


Product Type	Wireless and radiating connector
Product Brand	HELIAX®
Product Series	LDF2-50
General Specifications	
Body Style	Straight
Cable Family	LDF2-50
Inner Contact Attachment Method	Captivated
Inner Contact Plating	Silver
Interface	4.3-10 Male
Mounting Angle	Straight
Outer Contact Attachment Method	Self-flare
Outer Contact Plating	Trimetal
Dimensions	
Length	50.55 mm   1.99 in
Diameter	23.88 mm   0.94 in
Nominal Size	3/8 in

### Outline Drawing

Page 1 of 4



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025



### **Electrical Specifications**

3rd Order IMD at Frequency	-116 dBm @ 1800 MHz
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers
3rd Order IMD Dynamic, typical	-116 dB
Insertion Loss Coefficient, typical	0.05
Average Power at Frequency	700.0 W @ 900 MHz
Cable Impedance	50 ohm
Connector Impedance	50 ohm
dc Test Voltage	2500 V
Inner Contact Resistance, maximum	0.8 m0hm
Insulation Resistance, minimum	5000 MOhm
Operating Frequency Band	0 – 6000 MHz
Outer Contact Resistance, maximum	1.5 mOhm
Peak Power, maximum	10 kW
RF Operating Voltage, maximum (vrms)	707 V
Shielding Effectiveness	-110 dB

Page 2 of 4



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

# L2HM-D

### VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
45–2700 MHz	1.041	33.94
2700–4000 MHz	1.052	31.92
4000-6000 MHz	1.106	25.96

### Mechanical Specifications

Attachment Durability	25 cycles
Connector Retention Tensile Force	671.68 N   151 lbf
Connector Retention Torque	2.7 N-m   23.897 in lb
Coupling Nut Proof Torque	10 N-m   88.507 in lb
Coupling Nut Retention Force	669.99 N   150.62 lbf
Interface Durability	100 cycles
Interface Durability Method	IEC 61169-4:9.5
Mechanical Shock Test Method	IEC 60068-2-27

### **Environmental Specifications**

Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Attenuation, Ambient Temperature	20 °C   68 °F
Average Power, Ambient Temperature	40 °C   104 °F
Corrosion Test Method	IEC 60068-2-11
Immersion Depth	1 m
Immersion Test Mating	Mated
Immersion Test Method	IEC 60529:2001, IP68
Moisture Resistance Test Method	IEC 60068-2-3
Thermal Shock Test Method	IEC 60068-2-14
Vibration Test Method	IEC 60068-2-6
Water Jetting Test Mating	Mated
Water Jetting Test Method	IEC 60529:2001, IP66

#### Packaging and Weights

Page 3 of 4



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

## L2HM-D

#### Weight, net

Agency

75.96 g | 0.167 lb

#### Regulatory Compliance/Certifications

#### Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

#### \* Footnotes

Insertion Loss Coefficient, typical	0.05√ <sup>-</sup> freq (GHz) (not applicable for elliptical waveguide)
-------------------------------------	---

Immersion Depth Immersion at specified depth for 24 hours

Page 4 of 4

