


# F2A-DMDR-P

Base Product



## Product Classification

Product Type	Wireless transmission cable assembly
Product Brand	HELIAX®   SureFlex®
Product Series	FSJ2-50

## General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Interface, Connector A	7-16 DIN Male
Interface, Connector B	7-16 DIN Male
Specification Sheet Revision Level	A
Variable Length	For custom lengths, contact your local ANDREW representative

## Dimensions

Nominal Size	3/8 in
--------------	--------

## Electrical Specifications

3rd Order IMD Static	-110 dBm
3rd Order IMD Static Test Method	Two +43 dBm carriers

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.11	26.4
1700–2200 MHz	1.11	26.4
2200–2700 MHz	1.11	26.4

## Jumper Assembly Sample Label

# F2A-DMDR-P



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Included Products

- |          |   |   |
|----------|---|---|
| F2TDM-LS | - | 7-16 DIN Male for 3/8 in foam and air coaxial cable, factory attached                         |
| F2TDR-LS | - | 7-16 DIN Male Right Angle for 3/8 in foam and air coaxial cable, factory attached             |
| FSJ2-50  | - | FSJ2-50, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket |